

Terminal block	Conductor cross section [mm ²]														Recommended tightening torque [Nm]
	2.5	4	6	10	16	25	35	50	70	95	120	150	185	250	
UT 2,5 (-PE)	RE	RE													0.6
UT 4 (-PE)	RE	RE	RE												0.8
UT 6 (-PE)	RE	RE	RE	RE											1.8
UT 10 (-PE)	RE	RE	RE	RE	RE										1.8
UT 16 (-PE)	RE	RE	RE	RE	RE	RE									3.0
UT 35 (-PE)	RE	RE	RE	RE	RE	RE	RE								3.7
UKH 25			RE	RE	RE	RE									4.5
UKH 50							RE	SE							8
UKH 70								SE	SE						10
UKH 95									SE	SE					20
UKH 150											SE	SE			30
UKH 240													SE	SE	30

RE

Round, single-strand, class 1; approved

SE

Sector-shaped, single-strand, class 1 $\alpha = 90^\circ$; approved