





































Cross section	DIN 46228-4	UL486-F (Form E)	NF C 63-023	Special color code
0.14 mm ²				 Gray
0.25 mm ²				 Light blue
0.34 mm ²			 Green	 Turquoise
0.50 mm ²	 White	 White	 White	 Orange
0.75 mm ²	 Gray	 Gray	 Blue	 White
1.00 mm ²	 Red	 Red	 Red	 Yellow
1.50 mm ²	 Black	 Black	 Black	 Red
2.50 mm ²	 Blue	 Blue	 Gray	 Blue
4.00 mm ²	 Gray	 Gray	 Orange	 Gray
6.00 mm ²	 Yellow	 Yellow	 Green	 Black
10.00 mm ²	 Red	 Red	 Brown	 Ivory
16.00 mm ²	 Blue	 Blue	 Ivory	 Green
25.00 mm ²	 Yellow	 Yellow	 Black	 Brown
35.00 mm ²	 Red	 Red	 Red	 Beige
50.00 mm ²	 Blue	 Blue	 Blue	 Olive