

BL2 BPC 2000 8GB 120GB W10 2016 - Box PC



1092045

<https://www.phoenixcontact.com/gb/products/1092045>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Box PC with, Intel® Pentium® N4200 1.1/2.5 GHz, 1x COM (RS-232/422/485), 2x COM (RS-232), 2x USB 2.0, 2x USB 3.0. (bus system:)



Commercial data

Item number	1092045
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DRBABA
Product key	DRBABA
GTIN	4055626906461
Weight per piece (including packing)	1.93 g
Weight per piece (excluding packing)	1.57 g
Customs tariff number	84715000
Country of origin	TW

1092045

<https://www.phoenixcontact.com/gb/products/1092045>

Technical data

Product properties

Product type	Box PC
--------------	--------

Computer data

Processor	Intel® Pentium® N4200 1.1/2.5 GHz
RAM	8 GB DDR3 SODIMM
Cooling	passive

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

Interfaces

Interfaces	1x COM (RS-232/422/485)
	2x COM (RS-232)
	2x USB 2.0
	2x USB 3.0
Monitor output	2x DisplayPort
LAN chipset	Intel® I210-AT

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-5 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Approvals

Conformity/Approvals

UL, USA / Canada	UL 61010-2-201
------------------	----------------

Mounting

Mounting type	Panel mounting
	DIN rail mounting

1092045

<https://www.phoenixcontact.com/gb/products/1092045>

Classifications

ECLASS

ECLASS-11.0

19200102

ETIM

ETIM 9.0

EC001413

UNSPSC

UNSPSC 21.0

43211500

1092045

<https://www.phoenixcontact.com/gb/products/1092045>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	1, 2-dimethoxyethane; ethylene glycol dimethyl ether (EGDME)(CAS: 110-71-4)
	Lead(CAS: 7439-92-1)

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk