

# US-PML-P100 (D50) CUS - Prohibition sign



1014219

<https://www.phoenixcontact.com/gb/products/1014219>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Prohibition sign, can be ordered: by card, red/white, labeled according to customer specifications: Diagonal bar, mounting type: adhesive, diameter: 50 mm, Number of individual labels: 4, text field height: 50 mm, text field width: 50 mm



## Your advantages

- UniSheet - stick-on prohibition signs, color preprinted without symbol

## Commercial data

Item number	1014219
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BG8159
Product key	BG8159
Catalog page	Page 326 (C-5-2013)
GTIN	4046356786768
Weight per piece (including packing)	5 g
Weight per piece (excluding packing)	5 g
Customs tariff number	49119900
Country of origin	PL

## Technical data

### Product properties

Product type	Prohibition sign printed
Area of application	Prohibition marking according to ISO 7010
Type	circular

### Marking

Number of individual labels	4
Number of individual labels per row	2
Printing	Diagonal bar
Identification technology	Thermal transfer

### Dimensions

Width	0 mm
Text field width	50.00 mm
Height	0 mm
Text field height	50.00 mm
Depth	0.09 mm
Diameter	50.00 mm
Min. material thickness	0.09 mm

### Material specifications

Color	multicolored
	red (RAL 3001)
	white (RAL 9010)
Material	PVC
Components	Silicone-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Ambient temperature (assembly)	> 10 °C
Recommended ambient temperature (storage/transport)	22 °C
Recommended humidity (storage/transport)	50 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Mounting

Mounting type	adhesive
---------------	----------

# US-PML-P100 (D50) CUS - Prohibition sign



1014219

<https://www.phoenixcontact.com/gb/products/1014219>

## Classifications

### ECLASS

ECLASS-11.0	40200202
ECLASS-12.0	40200202
ECLASS-13.0	40200202

### ETIM

ETIM 9.0	EC001777
----------	----------

### UNSPSC

UNSPSC 21.0	55121700
-------------	----------

# US-PML-P100 (D50) CUS - Prohibition sign



1014219

<https://www.phoenixcontact.com/gb/products/1014219>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)