

US-PML-P200 (D100) CUS - Prohibition sign



1014224

<https://www.phoenixcontact.com/gb/products/1014224>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Prohibition sign, can be ordered: by card, white, labeled according to customer specifications: Blank, mounting type: adhesive, diameter: 100 mm, Number of individual labels: 1, text field height: 100 mm, text field width: 100 mm



Your advantages

- UniSheet - stick-on prohibition sign, unprinted

Commercial data

Item number	1014224
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BG8159
Product key	BG8159
Catalog page	Page 326 (C-5-2013)
GTIN	4046356786799
Weight per piece (including packing)	10.4 g
Weight per piece (excluding packing)	10.4 g
Customs tariff number	49119900
Country of origin	PL

US-PML-P200 (D100) CUS - Prohibition sign



1014224

<https://www.phoenixcontact.com/gb/products/1014224>

Technical data

Product properties

Product type	Prohibition sign printed
Area of application	Prohibition marking according to ISO 7010
Type	circular

Marking

Number of individual labels	1
Number of individual labels per row	1
Printing	Blank
Identification technology	Thermal transfer

Dimensions

Width	0 mm
Text field width	100.00 mm
Height	0 mm
Text field height	100.00 mm
Depth	0.09 mm
Diameter	100.00 mm
Min. material thickness	0.09 mm

Material specifications

Color	white (RAL 9010)
Material	PVC
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Ambient temperature (assembly)	> 10 °C
Recommended ambient temperature (storage/transport)	22 °C
Recommended humidity (storage/transport)	50 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

US-PML-P200 (D100) CUS - Prohibition sign



1014224

<https://www.phoenixcontact.com/gb/products/1014224>

Classifications

ECLASS

ECLASS-11.0	40200202
ECLASS-12.0	40200202
ECLASS-13.0	40200202

ETIM

ETIM 9.0	EC001777
----------	----------

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

US-PML-P200 (D100) CUS - Prohibition sign



1014224

<https://www.phoenixcontact.com/gb/products/1014224>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk