

# UPS-BAT-KIT/PB/2X12V/4AH - Uninterruptible power supply replacement battery



1283116

<https://www.phoenixcontact.com/us/products/1283116>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Replacement battery, VRLA-AGM, 2x12 V DC, 4 Ah. Only for 1274117 UPS-BAT/PB/24DC/4AH, 2320267 QUINT-UPS/24DC/24DC/10/3.4AH from V/C 06, 2905908 TRIO-UPS-2G/1AC/1AC/120V/750VA, and 2905909 TRIO-UPS-2G/1AC/1AC/230V/750VA

## Commercial data

Item number	1283116
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CM24
Product key	CMUEV3
GTIN	4063151487676
Weight per piece (including packing)	2,950 g
Weight per piece (excluding packing)	2,950 g
Customs tariff number	85072080
Country of origin	CN

# UPS-BAT-KIT/PB/2X12V/4AH - Uninterruptible power supply replacement battery



1283116

<https://www.phoenixcontact.com/us/products/1283116>

## Technical data

### Energy storage

#### Input

Input voltage	2x 12 V
Nominal capacity	4 Ah

#### General

Battery type	BB Battery HR4.2-12FR
Battery technology	VRLA-AGM
IQ-Technology	no
Latest startup date (battery only)	6 Months (0 °C ... 20 °C)
Latest startup (battery only) - range	3 Months ... 6 Months (20 °C ... 30 °C) 1 Months ... 3 Months (30 °C ... 40 °C)
Accumulator module service life (according to Eurobat)	6 (20 °C)
Disposal	Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations.

### Product properties

Product type	Battery unit
Product family	Replacement battery
Disposal	Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations.

#### Insulation characteristics

Protection class	III
Degree of pollution	2

### Dimensions

#### Item dimensions

Width	82 mm
Height	142 mm
Depth	102 mm

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (storage/transport)	-20 °C ... 40 °C
Ambient temperature (charge)	0 °C ... 40 °C
Ambient temperature (discharge)	-20 °C ... 50 °C

# UPS-BAT-KIT/PB/2X12V/4AH - Uninterruptible power supply replacement battery



1283116

<https://www.phoenixcontact.com/us/products/1283116>

Max. permissible relative humidity (operation)
--

≤ 95 %
--------

## Ex data

Suited for EX-applications
----------------------------

No
----

# UPS-BAT-KIT/PB/2X12V/4AH - Uninterruptible power supply replacement battery



1283116

<https://www.phoenixcontact.com/us/products/1283116>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1283116>



**GOST-R**

Approval ID: ROSS DE.BL08.D00191



**EAC**

Approval ID: RU\*DE\*01.B.78948/21

# UPS-BAT-KIT/PB/2X12V/4AH - Uninterruptible power supply replacement battery



1283116

<https://www.phoenixcontact.com/us/products/1283116>

## Classifications

### ECLASS

ECLASS-11.0	27059090
ECLASS-12.0	27059090
ECLASS-13.0	27059090

### ETIM

ETIM 9.0	EC011878
----------	----------

### UNSPSC

UNSPSC 21.0	26111700
-------------	----------

# UPS-BAT-KIT/PB/2X12V/4AH - Uninterruptible power supply replacement battery



1283116

<https://www.phoenixcontact.com/us/products/1283116>

## Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 8
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)