

WG-D HF 20,3 - Cable driller



3241107

<https://www.phoenixcontact.com/us/products/3241107>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable drillers, for fast and tool-free bundling of conductors and cables, removable and reusable



Commercial data

Item number	3241107
Packing unit	1 pc
Minimum order quantity	100 pc
Sales key	BE07
Product key	BE7133
Catalog page	Page 623 (C-3-2019)
GTIN	4046356717366
Weight per piece (including packing)	0.888 g
Weight per piece (excluding packing)	0.838 g
Customs tariff number	39269097
Country of origin	TW

Technical data

Product properties

Product type	Cable tie
Type	Notched strip
Tensile strength GRP	0 N

Dimensions

Width	20.3 mm
Length	39.4 mm

Material specifications

Color	transparent
Material	PA 6.6
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Cable/line

External cable diameter	17.8 mm ... 20.3 mm
Tensile strength	0 N

Environmental and real-life conditions

Ambient conditions

Optimum ambient temperature (storage/transport)	23 °C 50 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat.
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 60 °C
Resistance to UV radiation	no

Standards and regulations

Resistance to UV radiation	no
----------------------------	----

Mounting

Mounting type	Twist
---------------	-------

WG-D HF 20,3 - Cable driller



3241107

<https://www.phoenixcontact.com/us/products/3241107>

Classifications

ECLASS

ECLASS-11.0	27140702
ECLASS-12.0	27140702
ECLASS-13.0	27140702

ETIM

ETIM 9.0	EC000046
----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

WG-D HF 20,3 - Cable driller

3241107

<https://www.phoenixcontact.com/us/products/3241107>



Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com