

# WT-HF 4,5X160 BK - Cable tie



3240757

<https://www.phoenixcontact.com/us/products/3240757>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders for quick and secure bundling, standard version

## Commercial data

Item number	3240757
Packing unit	1 pc
Minimum order quantity	100 pc
Sales key	BE07
Product key	BE7131
Catalog page	Page 615 (C-3-2019)
GTIN	4046356704755
Weight per piece (including packing)	1.06 g
Weight per piece (excluding packing)	1.026 g
Customs tariff number	39269097
Country of origin	HR

# WT-HF 4,5X160 BK - Cable tie



3240757

<https://www.phoenixcontact.com/us/products/3240757>

## Technical data

### Product properties

Product type	Cable tie
Type	Internal teeth
Tensile strength GRP	220 N

### Dimensions

Width	4.5 mm
Length	160 mm

### Material specifications

Color	black
Material	PA 6.6
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

### Cable/line

External cable diameter	2.5 mm ... 40 mm
Tensile strength	220 N

### Environmental and real-life conditions

#### Ambient conditions

Optimum ambient temperature (storage/transport)	23 °C 50 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat.
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 60 °C
Resistance to UV radiation	no
Short-term temperature	110 °C

### Standards and regulations

Resistance to UV radiation	no
----------------------------	----

### Mounting

Mounting type	Cannot be removed
---------------	-------------------

# WT-HF 4,5X160 BK - Cable tie



3240757

<https://www.phoenixcontact.com/us/products/3240757>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240757>



UL Recognized



LR

# WT-HF 4,5X160 BK - Cable tie



3240757

<https://www.phoenixcontact.com/us/products/3240757>

## Classifications

### ECLASS

ECLASS-11.0	27140702
ECLASS-12.0	27140702
ECLASS-13.0	27140702

### ETIM

ETIM 9.0	EC000046
----------	----------

### UNSPSC

UNSPSC 21.0	39121700
-------------	----------

# WT-HF 4,5X160 BK - Cable tie

3240757

<https://www.phoenixcontact.com/us/products/3240757>



## Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

# WT-HF 4,5X160 BK - Cable tie

3240757

<https://www.phoenixcontact.com/us/products/3240757>



## Accessories

### UNIFOX-CT 4,8 - Cable tie tool

1212475

<https://www.phoenixcontact.com/us/products/1212475>



**Cable binder pliers**, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm

---

### UNIFOX-CT 4,8P - Cable tie tool

1212609

<https://www.phoenixcontact.com/us/products/1212609>



**Cable binder pliers**, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm

---

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)