

WP-GR HF CTA M25 BK - Corrugated tube screw connection



3241221

<https://www.phoenixcontact.com/us/products/3241221>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Corrugated pipe adapter, with internal thread, for connecting corrugated pipes to HEAVYCON EVO M25 plastic cable glands or ADVANCE M25 plastic housings, straight, black, IP66.

Commercial data

Item number	3241221
Packing unit	1 pc
Minimum order quantity	10 pc
Sales key	BF68
Product key	BF7DSA
Catalog page	Page 585 (C-4-2013)
GTIN	4046356860833
Weight per piece (including packing)	21.65 g
Weight per piece (excluding packing)	20.324 g
Customs tariff number	39269097
Country of origin	DE

WP-GR HF CTA M25 BK - Corrugated tube screw connection



3241221

<https://www.phoenixcontact.com/us/products/3241221>

Technical data

Product properties

Product type	Corrugated pipe screw connection
Application	Cable gland
Type	Internal thread
Thread type	metric

Material specifications

Material	PA 6
Flammability rating according to UL 94	V2
Material for screw connection	PA
Components	free from silicone, halogen, and cadmium

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C ... 115 °C

Mounting

Assembly instructions	The corrugated pipe adapter is used in the screw connection instead of the union nut. Thanks to the adapter, corrugated pipes can be used.
-----------------------	--

WP-GR HF CTA M25 BK - Corrugated tube screw connection



3241221

<https://www.phoenixcontact.com/us/products/3241221>

Classifications

ECLASS

ECLASS-11.0	27430311
ECLASS-13.0	27430311
ECLASS-12.0	27430311

ETIM

ETIM 9.0	EC001178
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

WP-GR HF CTA M25 BK - Corrugated tube screw connection



3241221

<https://www.phoenixcontact.com/us/products/3241221>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

WP-GR HF CTA M25 BK - Corrugated tube screw connection



3241221

<https://www.phoenixcontact.com/us/products/3241221>

Accessories

WP-PA HF-SL 28,5 BK - Protective hose

3240846

<https://www.phoenixcontact.com/us/products/3240846>



Protective hose, material: PA, UV-resistant: yes, flexible, degree of protection: IP40, color: black, flammability rating in acc. with UL 94: HB, inner diameter: 23 mm, Total length: 10 m

WP-PA HF 28,5 BK - Protective hose

3240684

<https://www.phoenixcontact.com/us/products/3240684>



Protective hose, material: PA 6, UV-resistant: yes, flexible, degree of protection: IP68, color: black, flammability rating in acc. with UL 94: V0, inner diameter: 23 mm, Total length: 50 m

WP-GR HF CTA M25 BK - Corrugated tube screw connection



3241221

<https://www.phoenixcontact.com/us/products/3241221>

WP-PA HF-HB 28,5 BK - Protective hose

3240842

<https://www.phoenixcontact.com/us/products/3240842>



Protective hose, material: PA 6, UV-resistant: yes, flexible, degree of protection: IP68, color: black, flammability rating in acc. with UL 94: HB, inner diameter: 23 mm, Total length: 50 m

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com