

WP-STEEL ZC 36 - Protective hose



3240700

<https://www.phoenixcontact.com/us/products/3240700>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hose, material: Steel, galvanized, degree of protection: IP40, color: silver, inner diameter: 31 mm, Total length: 10 m

Commercial data

Item number	3240700
Packing unit	1 m
Minimum order quantity	1 m
Sales key	BF68
Product key	BF7DSA
Catalog page	Page 596 (C-3-2019)
GTIN	4046356737203
Weight per piece (including packing)	5,200 g
Weight per piece (excluding packing)	5,200 g
Customs tariff number	83071000
Country of origin	DE

WP-STEEL ZC 36 - Protective hose



3240700

<https://www.phoenixcontact.com/us/products/3240700>

Technical data

Notes

General	Protective hose length is measured stretched out; length tolerance $\pm 5\%$
---------	--

Product properties

Product type	Corrugated pipe
Tensile strength GRP	500 N

Dimensions

Internal dimensions

Internal diameter	31 mm
-------------------	-------

Material specifications

Material	Steel, galvanized
Components	halogen-free

Cable/line

Bending radius, dynamic	150 mm
Bending radius, static	60 mm
Tensile strength	500 N
Halogen-free	yes

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP40
Ambient temperature (operation)	-50 °C ... 250 °C

WP-STEEL ZC 36 - Protective hose



3240700

<https://www.phoenixcontact.com/us/products/3240700>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240700>



VDE Zeichengenehmigung

WP-STEEL ZC 36 - Protective hose



3240700

<https://www.phoenixcontact.com/us/products/3240700>

Classifications

ECLASS

ECLASS-11.0	27430301
ECLASS-13.0	27430301
ECLASS-12.0	27430301

ETIM

ETIM 9.0	EC001179
----------	----------

UNSPSC

UNSPSC 21.0	40141700
-------------	----------

WP-STEEL ZC 36 - Protective hose



3240700

<https://www.phoenixcontact.com/us/products/3240700>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

WP-STEEL ZC 36 - Protective hose

3240700

<https://www.phoenixcontact.com/us/products/3240700>



Accessories

WP-SC BRASS 36 - Cable protection end sleeve

3241070

<https://www.phoenixcontact.com/us/products/3241070>



Cable protection end sleeve, material: Brass, nickel-plated, color: silver, inner diameter: 30 mm

WP-G BRASS IP40 PG29 - Screw connection

3241042

<https://www.phoenixcontact.com/us/products/3241042>



Cable gland made from brass with Pg thread, IP40 protection

WP-STEEL ZC 36 - Protective hose

3240700

<https://www.phoenixcontact.com/us/products/3240700>



WP-G BRASS IP40 M32 - Screw connection

3241049

<https://www.phoenixcontact.com/us/products/3241049>



Cable gland made from brass with metric thread, IP40 protection

WP-GT BRASS PG29 - Screw connection

3241028

<https://www.phoenixcontact.com/us/products/3241028>



Cable gland made from brass with Pg thread, rotatable, IP40 protection

WP-STEEL ZC 36 - Protective hose

3240700

<https://www.phoenixcontact.com/us/products/3240700>



WP-GT BRASS M32 - Screw connection

3241035

<https://www.phoenixcontact.com/us/products/3241035>



Cable gland made from brass with metric thread, rotatable, IP40 protection

WP-BASE HF 37 - Hose clamp

3240972

<https://www.phoenixcontact.com/us/products/3240972>



Hose clamp, material: Steel, galvanized, color: black/silver

WP-STEEL ZC 36 - Protective hose

3240700

<https://www.phoenixcontact.com/us/products/3240700>



WP-BASE A PG29 - Protective hose fixing bracket

3241081

<https://www.phoenixcontact.com/us/products/3241081>



Fixing bracket for protective sleeves, fixed with two screws

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com