

EMPPR (27X15) - Touch protection



0829535

<https://www.phoenixcontact.com/us/products/0829535>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Touch protection, Sheet, transparent, unlabeled, mounting type: snapped, lettering field size: 27 x 15 mm



Your advantages

- High level of mechanical and chemical stability
- Suitable for permanent outdoor use
- Stuck or snapped onto labeled CARRIER ... to protect the labeling
- Extremely thick, yet flexible and transparent shock protection

Commercial data

Item number	0829535
Packing unit	1 pc
Minimum order quantity	50 pc
Sales key	BG18
Product key	BG241B
Catalog page	Page 349 (C-3-2019)
GTIN	4046356614931
Weight per piece (including packing)	0.193 g
Weight per piece (excluding packing)	0.1 g
Customs tariff number	39204910
Country of origin	DE

EMPPR (27X15) - Touch protection



0829535

<https://www.phoenixcontact.com/us/products/0829535>

Technical data

Product properties

Product type	Cover
--------------	-------

Dimensions

Width	27 mm
Length	15 mm

Material specifications

RoHS compliant	yes
Foil strength	300 µm
Color	transparent
Material	PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05 (following)
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-30 °C ... 70 °C
Recommended storage conditions	10-30 °C / 40-70 % relative humidity. Storage in a cool and dry place is recommended.
Recommended ambient temperature (storage/transport)	-10 °C ... 30 °C
Recommended humidity (storage/transport)	70 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

EMPPR (27X15) - Touch protection



0829535

<https://www.phoenixcontact.com/us/products/0829535>

Mounting

Mounting type
snapped

EMPPR (27X15) - Touch protection



0829535

<https://www.phoenixcontact.com/us/products/0829535>

Classifications

ECLASS

ECLASS-11.0	24292214
ECLASS-12.0	24292214
ECLASS-13.0	24292214

ETIM

ETIM 9.0	EC002113
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com