

# EML-LPR (70X50)R SR - Label



1090080

<https://www.phoenixcontact.com/us/products/1090080>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, silver, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, lettering field size: 70 x 50 mm, Number of individual labels: 750

## Your advantages

- EML-LPR ... self-adhesive device markers for identification of various types of equipment in controller, system, and control cabinet building
- The EML-LPR labels feature a protective laminate, which is adhered to the entire printing surface after the label has been attached. The printed information is protected from external influences
- The protective laminate is attached to the label. The edge is perforated, simplifying adhesion
- Thanks to its great adhesive strength, this label can be placed on rough, textured, and low-energy surfaces
- High-quality printing is achieved in combination with the THERMOMARK-RIBBON 110 ink ribbon

## Commercial data

Item number	1090080
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG16
Product key	BG2411
GTIN	4055626898698
Weight per piece (including packing)	1,265 g
Weight per piece (excluding packing)	1,200 g
Customs tariff number	39199080
Country of origin	DE

## Technical data

### Product properties

Product type	Device marking
Product property	With protective laminate

### Marking

Number of individual labels	750
Number of individual labels per row	1
Identification technology	Thermal transfer for rolls

### Mounting

Mounting type	adhesive
---------------	----------

### Material specifications

RoHS compliant	yes
Color	silver
Material	Polyester
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

#### Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

#### Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
---------------------------------	-------------------

# EML-LPR (70X50)R SR - Label



1090080

<https://www.phoenixcontact.com/us/products/1090080>

Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	2 years

## Dimensions

Width	70 mm
Length	50 mm

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Notes

General	For the THERMOMARK ROLL and THERMOMARK ROLL 2.0 roll printers, this material can only be processed with an external media hub.
General	Items are approved for smooth and textured stainless-steel surfaces as well as for surfaces that have been coated with hammer-finish paint.

# EML-LPR (70X50)R SR - Label



1090080

<https://www.phoenixcontact.com/us/products/1090080>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1090080>



**cULus Recognized**

Approval ID: MH48542

# EML-LPR (70X50)R SR - Label



1090080

<https://www.phoenixcontact.com/us/products/1090080>

## Classifications

### ECLASS

ECLASS-11.0	27281103
ECLASS-12.0	27281103
ECLASS-13.0	27281103

### ETIM

ETIM 8.0	EC001288
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# EML-LPR (70X50)R SR - Label

1090080

<https://www.phoenixcontact.com/us/products/1090080>



## Accessories

### THERMOMARK E.300 D US - Thermal transfer printer

1287033

<https://www.phoenixcontact.com/us/products/1287033>



Thermal transfer printer with internal rewinder for printing all materials in roll format with a print resolution of 300 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

---

### THERMOMARK E.300 US - Thermal transfer printer

1287021

<https://www.phoenixcontact.com/us/products/1287021>



Thermal transfer printer for printing all materials in roll format with a print resolution of 300 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

# EML-LPR (70X50)R SR - Label

1090080

<https://www.phoenixcontact.com/us/products/1090080>



## THERMOMARK E.600 D US - Thermal transfer printer

1287040

<https://www.phoenixcontact.com/us/products/1287040>



Thermal transfer printer with internal rewinder for printing all materials in roll format with a print resolution of 600 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

---

## THERMOMARK E.600 US - Thermal transfer printer

1287029

<https://www.phoenixcontact.com/us/products/1287029>



Thermal transfer printer for printing all materials in roll format with a print resolution of 600 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

# EML-LPR (70X50)R SR - Label

1090080

<https://www.phoenixcontact.com/us/products/1090080>



## THERMOMARK ROLL 2.0 - Thermal transfer printer

1085260

<https://www.phoenixcontact.com/us/products/1085260>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

---

## THERMOMARK-RIBBON 110 - Ink ribbon

5145384

<https://www.phoenixcontact.com/us/products/5145384>



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., length: 300 m, roll length: 300 m, width: 110 mm, color: black



# EML-LPR (70X50)R SR - Label

1090080

<https://www.phoenixcontact.com/us/products/1090080>



## THERMOMARK-RIBBON 110/50 - Ink ribbon

0800687

<https://www.phoenixcontact.com/us/products/0800687>



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., length: 50 m, roll length: 50 m, width: 110 mm, color: black

---

## THERMOMARK ROLL-ERH - Media hub

5146448

<https://www.phoenixcontact.com/us/products/5146448>



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

# EML-LPR (70X50)R SR - Label

1090080

<https://www.phoenixcontact.com/us/products/1090080>



## THERMOMARK ROLLMASTER 300 - Thermal transfer printer

0804501

<https://www.phoenixcontact.com/us/products/0804501>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

---

## THERMOMARK ROLLMASTER 600 - Thermal transfer printer

0804663

<https://www.phoenixcontact.com/us/products/0804663>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

# EML-LPR (70X50)R SR - Label

1090080

<https://www.phoenixcontact.com/us/products/1090080>



## THERMOMARK ROLL - Thermal transfer printer

5146477

<https://www.phoenixcontact.com/us/products/5146477>



Thermal transfer printer, 300 dpi, incl. European power cable, US power cable, and USB cable. DVD with CLIP PROJECT advanced planning and marking software, user manuals in various languages, Windows® printer driver, and firmware. German/English user manual in DIN A5 format, EML (20x8)R roll of labels, white, with 1000 labels, and ink ribbon: 50 m

---

## THERMOMARK X1.2 - Thermal transfer printer

5146231

<https://www.phoenixcontact.com/us/products/5146231>



Thermal transfer printer, weight: 10 kg, length: 0.446 m, width: 242 mm, height: 274 mm, color: gray

---

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)