

D L 2,8 64X 8 - Display

2203543

<https://www.phoenixcontact.com/us/products/2203543>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Graphic LCD module, 2.8", 128 x 64 pixels, FSTN transfective/positive 6:00, LED backlight, interface: 8 bit, operating temperature: -20 °C ... 70 °C



Your advantages

- Graphic LCD module
- Easy and time-saving integration into HCS series electronics housings
- Long-term availability
- Ideal protective shield and gasket material
- Backlighting can be switched on and off
- Common interface for your electronics

Commercial data

Item number	2203543
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC05
Product key	ACGAAA
GTIN	4055626481975
Weight per piece (including packing)	56.2 g
Weight per piece (excluding packing)	26 g
Customs tariff number	85299020
Country of origin	DE

D L 2,8 64X 8 - Display



2203543

<https://www.phoenixcontact.com/us/products/2203543>

Technical data

Notes

General	The background color may vary slightly depending on the ambient temperature. This procedure can be reversed.
General	NOTE: Electrostatic discharge! The device contains components that can be damaged or destroyed by electrostatic discharge. When handling the device, observe the necessary safety precautions against electrostatic discharge (ESD) according to EN 61340-5-1 and IEC 61340-5-1.

Product properties

Product type	Display
--------------	---------

Display

Display type	Graphic LCD module
Display type	LCD with backlighting
Display type	Transmissive
Panel technology	FSTN
Diagonals (cm)	7.11 cm
Diagonals (inch)	2.8 in.
Screen resolution	128 x 64 Pixel(s)
Display lighting type	LED, white
Contrast ratio	4
Viewing direction	6:00
Controller	NT7538
Representation	positive

Interfaces

Interface	8-bit parallel
-----------	----------------

Dimensions

Dimensions	70 mm x 49 mm x 5 mm (Mounting panel dimensions)
	63 mm x 35 mm (Viewing area)
	60 mm x 30 mm (Active range)

Material specifications

Surface characteristics	untreated
-------------------------	-----------

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 55 - 10 Hz
Sweep speed	1 octave/min
Test duration per axis	15 min.

D L 2,8 64X 8 - Display

2203543

<https://www.phoenixcontact.com/us/products/2203543>



Test directions	X-, Y- and Z-axis
-----------------	-------------------

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 80 °C
Relative humidity (storage/transport)	93 %

Mounting

Mounting type	Screw mounting
---------------	----------------

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------

D L 2,8 64X 8 - Display

2203543

<https://www.phoenixcontact.com/us/products/2203543>



Classifications

ECLASS

ECLASS-11.0	27261890
ECLASS-12.0	27261890
ECLASS-13.0	27261890

ETIM

ETIM 9.0	EC011541
----------	----------

UNSPSC

UNSPSC 21.0	43211900
-------------	----------

D L 2,8 64X 8 - Display

2203543

<https://www.phoenixcontact.com/us/products/2203543>



Accessories

HCS-C MINI 1W C C C 7035 - Electronic housing

2203147

<https://www.phoenixcontact.com/us/products/2203147>



Handheld housing, C-Mini, light gray, consisting of two half shells with screws, front 1.1 mm recessed with window and keypad slot

HCS-C MINI 1W 9V 1 C 7035 - Electronic housing

2203150

<https://www.phoenixcontact.com/us/products/2203150>



Handheld housing, C-Mini, light gray, consisting of two half shells, front plate above, screws. Front 1.1 mm recessed, with window and keypad slot, battery compartment cover and battery contacts for 9 V battery

D L 2,8 64X 8 - Display

2203543

<https://www.phoenixcontact.com/us/products/2203543>



HCS-C MINI 1W 3AAA 1 1 7035 - Electronic housing

2203152

<https://www.phoenixcontact.com/us/products/2203152>



Handheld housing, C-Mini, light gray, consisting of two half shells, two front plates, screws. Front 1.1 mm recessed, with window and keypad slot, battery compartment cover and battery contacts for 3 AA batteries

HCS-C MINI-P 1W C C C 7035 - Electronic housing

2203153

<https://www.phoenixcontact.com/us/products/2203153>



Handheld housing, C-Mini-Plus, light gray, consisting of two half shells with screws, front 1.1 mm recessed, with window and keypad slot

D L 2,8 64X 8 - Display

2203543

<https://www.phoenixcontact.com/us/products/2203543>



HCS-C MINI-P 1W C 1 1 7035 - Electronic housing

2203155

<https://www.phoenixcontact.com/us/products/2203155>



Handheld housing, C-Mini-Plus, light gray, consisting of two half shells, two front plates with screws, front 1.1 mm recessed, with window and keypad slot

HCS-C MEDIUM 1W C 1 C 7035 - Electronic housing

2203162

<https://www.phoenixcontact.com/us/products/2203162>



Handheld housing, C-Medium, light gray, consisting of two half shells, front plates above with screws, front 1.1 mm recessed, with window and keypad slot

D L 2,8 64X 8 - Display

2203543

<https://www.phoenixcontact.com/us/products/2203543>



HCS-C MEDIUM 1W 3AA 1 1 7035 - Electronic housing

2203163

<https://www.phoenixcontact.com/us/products/2203163>



Handheld housing, C-Medium, light gray, consisting of two half shells, two front plates, screws. Front 1.1 mm recessed, with window and keypad slot, battery compartment cover and battery contacts for 3 AA batteries

HCS-T MINI 1W C C C 7035 - Electronic housing

2203131

<https://www.phoenixcontact.com/us/products/2203131>



Handheld housing, T-Mini, light gray, consisting of two half shells with screws, front 1.1 mm recessed, with window and keypad slot

D L 2,8 64X 8 - Display

2203543

<https://www.phoenixcontact.com/us/products/2203543>



HCS-T MINI 1W 3AA C C 7035 - Electronic housing

2203134

<https://www.phoenixcontact.com/us/products/2203134>



Handheld housing, T-Mini, light gray, consisting of two half shells with screws. Front 1.1 mm recessed, with window and keypad slot, battery compartment cover and battery contacts for 3 AA batteries

HCS-C MAXI 1W C C C 7035 - Electronic housing

2203166

<https://www.phoenixcontact.com/us/products/2203166>



Handheld housing, C-Maxi, light gray, consisting of two half shells with screws, front 1.1 mm recessed with window and keypad slot

D L 2,8 64X 8 - Display

2203543

<https://www.phoenixcontact.com/us/products/2203543>



HCS-C MAXI 1W C 1 1 7035 - Electronic housing

2203167

<https://www.phoenixcontact.com/us/products/2203167>



Handheld housing, C-Maxi, light gray, consisting of two half shells, two front plates with screws, front 1.1 mm recessed, with window and keypad slot

HCS-C MAXI 1W 2X3AA 1 1 7035 - Electronic housing

2203168

<https://www.phoenixcontact.com/us/products/2203168>



Handheld housing, C-Maxi, light gray, consisting of two half shells, two front plates, screws. Front 1.1 mm recessed, with window and keypad slot, battery compartment cover and battery contacts for 6 AA batteries

D L 2,8 64X 8 - Display

2203543

<https://www.phoenixcontact.com/us/products/2203543>



HCS-C MAXI 1W 2X9V 1 1 7035 - Electronic housing

2203170

<https://www.phoenixcontact.com/us/products/2203170>



Handheld housing, C-Maxi, light gray, consisting of two half shells, two front plates, screws. Front 1.1 mm recessed, with window and keypad slot, battery compartment cover and battery contacts for 2x 9 V battery

HCS-T MEDIUM 1W C 1 1 7035 - Electronic housing

2203138

<https://www.phoenixcontact.com/us/products/2203138>



Handheld housing, T-Medium, light gray, consisting of two half shells, two front plates with screws, front 1.1 mm recessed, with window and keypad slot

D L 2,8 64X 8 - Display

2203543

<https://www.phoenixcontact.com/us/products/2203543>



HCS-T MEDIUM 1W C C 1 7035 - Electronic housing

2203139

<https://www.phoenixcontact.com/us/products/2203139>



Handheld housing, T-Medium, light gray, consisting of two half shells, front plates below with screws, front 1.1 mm recessed, with window and keypad slot

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com