

# ME MAX B-12,5 KMGY - Filler plug



2914660

<https://www.phoenixcontact.com/us/products/2914660>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Filler plug for unoccupied terminal points, width: 11 mm, height: 21.6 mm, depth: 8.1 mm, color: light grey (7035)

## Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

## Commercial data

Item number	2914660
Packing unit	1 pc
Minimum order quantity	10 pc
Sales key	AC08
Product key	ACHABZ
Catalog page	Page 684 (C-1-2013)
GTIN	4046356051132
Weight per piece (including packing)	0.89 g
Weight per piece (excluding packing)	0.76 g
Customs tariff number	39269097
Country of origin	DE

# ME MAX B-12,5 KMGY - Filler plug



2914660

<https://www.phoenixcontact.com/us/products/2914660>

## Technical data

### Notes

General	Refer to the data sheet for the range in the download area.
---------	---

### Product properties

Product type	Filler plug
Product family	ME MAX B
Type	Filler plug for unoccupied terminal points
Housing type	DIN rail housing
Ventilation openings present	no
Housing series	ME-MAX

### Dimensions

Width	11 mm
Height	21.6 mm
Depth	8.1 mm

### Material specifications

Color	light grey (7035)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Surface characteristics	untreated
Housing material	Polyamide

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

### Mounting

Mounting type	Latching
---------------	----------

### Packaging specifications

Outer packaging type	Resealable bag
----------------------	----------------

# ME MAX B-12,5 KMGY - Filler plug



2914660

<https://www.phoenixcontact.com/us/products/2914660>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2914660>



**UL Recognized**

Approval ID: FILE E 240868

# ME MAX B-12,5 KMGY - Filler plug



2914660

<https://www.phoenixcontact.com/us/products/2914660>

## Classifications

### ECLASS

ECLASS-11.0	27182702
ECLASS-13.0	27190605

### ETIM

ETIM 9.0	EC001031
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# ME MAX B-12,5 KMGY - Filler plug



2914660

<https://www.phoenixcontact.com/us/products/2914660>

## Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e No hazardous substances above threshold values
------------	---

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)