

TM-RIBBON 25 BK 102 - Ink ribbon



1053499

<https://www.phoenixcontact.com/us/products/1053499>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, for printing WMS-OT/WMS-2 HF... materials, length: 300 m, roll length: 300 m, width: 25 mm, color: black

Commercial data

| | |
|--------------------------------------|--------------------|
| Item number | 1053499 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG02 |
| Product key | BG1223 |
| Catalog page | Page 42 (C-3-2019) |
| GTIN | 4055626685717 |
| Weight per piece (including packing) | 82 g |
| Weight per piece (excluding packing) | 22.22 g |
| Customs tariff number | 96121010 |
| Country of origin | DE |

TM-RIBBON 25 BK 102 - Ink ribbon



1053499

<https://www.phoenixcontact.com/us/products/1053499>

Technical data

Product properties

| | |
|--------------|------------|
| Product type | Ink ribbon |
|--------------|------------|

Marking

| | |
|---------------------------|------------------|
| Identification technology | Thermal transfer |
|---------------------------|------------------|

Dimensions

| | |
|----------------|-------|
| Width | 25 mm |
| Length | 300 m |
| Length of roll | 300 m |

Material specifications

| | |
|----------------|-------|
| RoHS compliant | yes |
| Color | black |

Environmental and real-life conditions

Ambient conditions

| | |
|--------------------------------|---|
| Recommended storage conditions | 5 - 35°C / 30 - 80 % relative humidity. Storage in a cool and dry place in the original packaging is recommended. |
|--------------------------------|---|

TM-RIBBON 25 BK 102 - Ink ribbon



1053499

<https://www.phoenixcontact.com/us/products/1053499>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 19140614 |
| ECLASS-12.0 | 19140614 |
| ECLASS-13.0 | 19140614 |

ETIM

| | |
|----------|----------|
| ETIM 8.0 | EC001694 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 44103100 |
|-------------|----------|

TM-RIBBON 25 BK 102 - Ink ribbon



1053499

<https://www.phoenixcontact.com/us/products/1053499>

Environmental product compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

TM-RIBBON 25 BK 102 - Ink ribbon

1053499

<https://www.phoenixcontact.com/us/products/1053499>



Accessories

THERMOMARK E.300 D US - Thermal transfer printer

1287033

<https://www.phoenixcontact.com/us/products/1287033>



Thermal transfer printer with internal rewinder for printing all materials in roll format with a print resolution of 300 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

THERMOMARK E.300 US - Thermal transfer printer

1287021

<https://www.phoenixcontact.com/us/products/1287021>



Thermal transfer printer for printing all materials in roll format with a print resolution of 300 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

TM-RIBBON 25 BK 102 - Ink ribbon

1053499

<https://www.phoenixcontact.com/us/products/1053499>



THERMOMARK E.600 D US - Thermal transfer printer

1287040

<https://www.phoenixcontact.com/us/products/1287040>



Thermal transfer printer with internal rewinder for printing all materials in roll format with a print resolution of 600 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

THERMOMARK E.600 US - Thermal transfer printer

1287029

<https://www.phoenixcontact.com/us/products/1287029>



Thermal transfer printer for printing all materials in roll format with a print resolution of 600 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

TM-RIBBON 25 BK 102 - Ink ribbon

1053499

<https://www.phoenixcontact.com/us/products/1053499>



THERMOMARK ROLL 2.0 - Thermal transfer printer

1085260

<https://www.phoenixcontact.com/us/products/1085260>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

THERMOMARK ROLLMASTER 300 - Thermal transfer printer

0804501

<https://www.phoenixcontact.com/us/products/0804501>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

TM-RIBBON 25 BK 102 - Ink ribbon

1053499

<https://www.phoenixcontact.com/us/products/1053499>



THERMOMARK ROLLMASTER 600 - Thermal transfer printer

0804663

<https://www.phoenixcontact.com/us/products/0804663>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

THERMOMARK ROLL - Thermal transfer printer

5146477

<https://www.phoenixcontact.com/us/products/5146477>



Thermal transfer printer, 300 dpi, incl. European power cable, US power cable, and USB cable. DVD with CLIP PROJECT advanced planning and marking software, user manuals in various languages, Windows® printer driver, and firmware. German/English user manual in DIN A5 format, EML (20x8)R roll of labels, white, with 1000 labels, and ink ribbon: 50 m

TM-RIBBON 25 BK 102 - Ink ribbon

1053499

<https://www.phoenixcontact.com/us/products/1053499>



THERMOMARK X1.2 - Thermal transfer printer

5146231

<https://www.phoenixcontact.com/us/products/5146231>



Thermal transfer printer, weight: 10 kg, length: 0.446 m, width: 242 mm, height: 274 mm, color: gray

THERMOMARK W2 - Thermal transfer printer

5146147

<https://www.phoenixcontact.com/us/products/5146147>



Thermal transfer printer for material off the roll, incl. Euro/US power cable, USB cable, and perforation knife. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English.

TM-RIBBON 25 BK 102 - Ink ribbon

1053499

<https://www.phoenixcontact.com/us/products/1053499>



THERMOMARK S1.1 - Thermal transfer printer

5146257

<https://www.phoenixcontact.com/us/products/5146257>



Thermal transfer printer, weight: 2 kg, length: 0.25 m, width: 230 mm, height: 170 mm, color: gray

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com