

# UCT-TMC (30X8) - Marker for end clamp



1278515

<https://www.phoenixcontact.com/us/products/1278515>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker for end clamp, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, lettering field size: 30 x 8 mm, Number of individual labels: 5

## Your advantages

- The UCT-TMC (30X8) ... UniCard marking card provides markers for the E/NS 35 N ... end bracket
- The markers, which are supplied in uniform sheets, can be marked quickly, easily, and precisely using the card printers
- The clip geometry enables the easy mounting and removal of the markers. For removal, the marker can be levered out with a screwdriver and the recess on the marker or simply unclipped, for example.
- The multi-section marking strips are easy to fit and can be easily separated if required
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

## Commercial data

Item number	1278515
Packing unit	1 pc
Minimum order quantity	7 pc
Sales key	BG07
Product key	BG2118
GTIN	4063151475499
Weight per piece (including packing)	12.585 g
Weight per piece (excluding packing)	10.75 g
Customs tariff number	39269097
Country of origin	PL

# UCT-TMC (30X8) - Marker for end clamp



1278515

<https://www.phoenixcontact.com/us/products/1278515>

## Technical data

### Notes

General	Can be labeled via thermal transfer
---------	-------------------------------------

### Product properties

Product type	Terminal marking
Area of application	E/NS 35 N end bracket

### Marking

Number of individual labels	5
Number of individual labels per row	1
Identification technology	Thermal transfer for sheets and cards, UV LED technology, direct laser marking

### Dimensions

Width	8 mm
Length	30 mm

### Material specifications

Color	white
Material	PC
Flammability rating according to UL 94	V2
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

#### Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

#### Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

# UCT-TMC (30X8) - Marker for end clamp



1278515

<https://www.phoenixcontact.com/us/products/1278515>

Specification	IEC 60068-2-2:2007-07
Result	Test passed
Duration	96 h
Temperature for testing	120 °C

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

## Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	2 years

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	snapped
---------------	---------

# UCT-TMC (30X8) - Marker for end clamp



1278515

<https://www.phoenixcontact.com/us/products/1278515>

## Classifications

### ECLASS

ECLASS-11.0	27281101
ECLASS-12.0	27281101
ECLASS-13.0	27281101

### ETIM

ETIM 9.0	EC000761
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# UCT-TMC (30X8) - Marker for end clamp



1278515

<https://www.phoenixcontact.com/us/products/1278515>

## Environmental product compliance

REACH SVHC

Perfluorobutane sulfonic acid (PFBS) and its salts

# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## Accessories

### THERMOMARK CARD 2.0 - Thermal transfer printer

1085267

<https://www.phoenixcontact.com/us/products/1085267>



Thermal transfer printer for card materials, including Euro/US power cable and USB cable. User manual printed in German and English. Magazine for UCT-TM... sheets and magazines for US-... cards. One packing unit each UCT-TM 6, US-EMLP (85,6x54), ink ribbon = 50 m

---

### THERMOMARK PRIME - Thermal transfer printer

5148888

<https://www.phoenixcontact.com/us/products/5148888>



Mobile thermal transfer printer for card materials, including power supply unit, Euro/US power cable, and USB cable. User manual printed in German and English. Magazine for UCT-TM... sheets and magazine for US-... cards. One packing unit each UCT-TM 6, US-EMLP (85,6x54), ink ribbon cartridge = 70 m

# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## BLUEMARK ID - Printer

1003334

<https://www.phoenixcontact.com/us/products/1003334>



Monochrome printer with UV LED technology and integrated "MARKING system app" identification software. 7" touch color display for printing plastic tags in UC, UCT, US, and UM format, as well as metal labels.

---

## BLUEMARK ID COLOR - Printer

1002329

<https://www.phoenixcontact.com/us/products/1002329>



CMYK multicolor printer with UV LED technology, with integrated "MARKING system app" identification software, 7" touch color display for printing plastic tags in UC, UCT, and UM format, as well as metal labels.

## UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## TOPMARK NEO - Laser marker

1012015

<https://www.phoenixcontact.com/us/products/1012015>



Laser marking system for the efficient marking of metal or plastic marking material from the LS..., UCT..., UC.../PP..., UM... product families.

---

## THERMOMARK-RIBBON 110/50-TC - Ink ribbon

0801384

<https://www.phoenixcontact.com/us/products/0801384>



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., length: 50 m, roll length: 50 m, width: 110 mm, color: black



# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## THERMOMARK-RIBBON 110-TC - Ink ribbon

0801371

<https://www.phoenixcontact.com/us/products/0801371>



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., length: 300 m, roll length: 300 m, width: 110 mm, color: black

---

## TMP-RIBBON 110 BK 100 - Ink ribbon cartridge

0803374

<https://www.phoenixcontact.com/us/products/0803374>



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups UCT. ..., US..., and UM..., length: 70 m, roll length: 70 m, width: 110 mm, color: black

# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## BM ID-CARTR. BK - Ink cartridge

1044345

<https://www.phoenixcontact.com/us/products/1044345>



Replacement UV fluid, 23 ml, color: black

---

## BM ID-CARTR. CY - Ink cartridge

1044346

<https://www.phoenixcontact.com/us/products/1044346>



Replacement UV fluid, 23 ml, color: cyan

# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## BM ID-CARTR. YE - Ink cartridge

1044348

<https://www.phoenixcontact.com/us/products/1044348>

Replacement UV fluid, 23 ml, color: yellow



---

## BLUEMARK CLED-FLUID-CARTR. - Ink cartridge

5146662

<https://www.phoenixcontact.com/us/products/5146662>

Cartridge, for replacement, 20 ml UV color, black, including cleaning cartridge



## UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## BLUEMARK FLUID-CARTRIDGE - Ink cartridge

5147421

<https://www.phoenixcontact.com/us/products/5147421>

Cartridge, for replacement, 28 ml UV color, black including cleaning cartridge



---

## TMP-UCT-MAG34 - Magazine

1281799

<https://www.phoenixcontact.com/us/products/1281799>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD..., for accommodating UCT-TMC (30x8), length: 0.166 m, width: 114 mm, height: 11.5 mm



# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## BM ID-MAG20 - Magazine

1044356

<https://www.phoenixcontact.com/us/products/1044356>



Infeed magazine for accommodating a max. of 20 UniCard sheets

---

## BM ID-MAG40 - Magazine

1044357

<https://www.phoenixcontact.com/us/products/1044357>



Infeed magazine for accommodating a maxi. of 40 UniCard sheets

# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>




## TOPMARK LASER-MAG UCT-A - Magazine

0803141

<https://www.phoenixcontact.com/us/products/0803141>

Magazine for the TOPMARK LASER, for accommodating UCT material automatically



---

## TOPMARK LASER-MAG UCT-M - Magazine

0803143

<https://www.phoenixcontact.com/us/products/0803143>

Magazine for the TOPMARK LASER, for accommodating UCT material manually



# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>




## E/NS 35 N - End bracket

0800886

<https://www.phoenixcontact.com/us/products/0800886>

End clamp, width: 9.5 mm, color: gray



---

## E/NS 35 N BK - End bracket

0804271

<https://www.phoenixcontact.com/us/products/0804271>

End bracket, material: PA, color: black



## UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## THERMOMARK CARD - Thermal transfer printer

5146464

<https://www.phoenixcontact.com/us/products/5146464>

Thermal transfer printer for cards



---

## BLUEMARK CLED - Printer

5147999

<https://www.phoenixcontact.com/us/products/5147999>

Printers with LED-UV technology for printing plastic labels in UniCard format.





# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## TOPMARK LASER - Laser marker

0831831

<https://www.phoenixcontact.com/us/products/0831831>



Laser marker and MARKING NOTEBOOK with German operating system and German keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

---

## TOPMARK LASER US - Laser marker

0803297

<https://www.phoenixcontact.com/us/products/0803297>



Laser marker and MARKING NOTEBOOK with English operating system and English keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 120 V extraction unit

# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## TOPMARK LASER SE SE - Laser marker

0803287

<https://www.phoenixcontact.com/us/products/0803287>



Laser marker and MARKING NOTEBOOK with Swedish operating system and Swedish keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit.

---

## TOPMARK LASER RU RU - Laser marker

0803286

<https://www.phoenixcontact.com/us/products/0803286>



Laser marker and MARKING NOTEBOOK with Russian operating system and Russian keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit.

# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## TOPMARK LASER PT PT - Laser marker

0803295

<https://www.phoenixcontact.com/us/products/0803295>



Laser marker and MARKING NOTEBOOK with Portuguese operating system and Portuguese keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

---

## TOPMARK LASER PL US - Laser marker

0803290

<https://www.phoenixcontact.com/us/products/0803290>



Laser marker and MARKING NOTEBOOK with Polish operating system and American keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## TOPMARK LASER IT IT - Laser marker

0803292

<https://www.phoenixcontact.com/us/products/0803292>



Laser marker and MARKING NOTEBOOK with Italian operating system and Italian keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

---

## TOPMARK LASER HU HU - Laser marker

0803299

<https://www.phoenixcontact.com/us/products/0803299>



Laser marker and MARKING NOTEBOOK with Hungarian operating system and Hungarian keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## TOPMARK LASER FR FR - Laser marker

0803291

<https://www.phoenixcontact.com/us/products/0803291>



Laser marker and MARKING NOTEBOOK with French operating system and French keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

---

## TOPMARK LASER ES ES - Laser marker

0803293

<https://www.phoenixcontact.com/us/products/0803293>



Laser marker and MARKING NOTEBOOK with Spanish operating system and Spanish keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## TOPMARK LASER DK DK - Laser marker

0803288

<https://www.phoenixcontact.com/us/products/0803288>



Laser marker and MARKING NOTEBOOK with Danish operating system and Danish keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

---

## TOPMARK LASER DE CH - Laser marker

0803285

<https://www.phoenixcontact.com/us/products/0803285>



Laser marker and MARKING NOTEBOOK with German operating system and German keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

# UCT-TMC (30X8) - Marker for end clamp

1278515

<https://www.phoenixcontact.com/us/products/1278515>



## TOPMARK LASER CN US - Laser marker

0803289

<https://www.phoenixcontact.com/us/products/0803289>



Laser marker and MARKING NOTEBOOK with Chinese operating system and American keyboard, incl. CLIP-PROJECT PROFESSIONAL software and installed drivers, user manual, sheet magazine, card magazine, and 230 V extraction unit

---

## E/NS 35 N BU - End bracket

0804376

<https://www.phoenixcontact.com/us/products/0804376>



End bracket, material: PA, color: blue

---

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)