

# OCS POLEFIX 0806 - Mounting material



1476923

<https://www.phoenixcontact.com/us/products/1476923>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mount for mast Ø of 60 mm ... 140 mm, complete set for a housing of 8" x 6", material: steel



## Your advantages

- Internationally certified housing system
- Special plastic ensures safe continuous operation
- Provides protection against the ingress of jet water
- Withstands even heavy mechanical strain

## Commercial data

Item number	1476923
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC04
Product key	ACFDBZ
GTIN	4063151897109
Weight per piece (including packing)	0.575 kg
Weight per piece (excluding packing)	0.382 kg
Customs tariff number	73269098
Country of origin	EE

# OCS POLEFIX 0806 - Mounting material



1476923

<https://www.phoenixcontact.com/us/products/1476923>

## Technical data

### Product properties

Product type	Mounting material
Housing type	Outdoor housing
Housing series	OCS

### Dimensions

Width	147 mm
Height	275 mm

### Material specifications

Color	Silver
Housing material	Steel

### Mounting

Mounting type	Mast mounting or wall mounting
---------------	--------------------------------

# OCS POLEFIX 0806 - Mounting material



1476923

<https://www.phoenixcontact.com/us/products/1476923>

## Classifications

### ECLASS

ECLASS-11.0	27182702
ECLASS-13.0	27190605

### ETIM

ETIM 9.0	EC001031
----------	----------

# OCS POLEFIX 0806 - Mounting material



1476923

<https://www.phoenixcontact.com/us/products/1476923>

## Mandatory accessories

### OCS HP 080604 GY7035 - Electronic housing

1471770

<https://www.phoenixcontact.com/us/products/1471770>



Outdoor housing, color: light gray, dimensions: 8" x 6" x 4", incl. corner inlays, cover plugs, screws, cover: light gray, plastic latch, material: PC UV-stabilized

### OCS HP 080604 TRANS - Electronic housing

1471772

<https://www.phoenixcontact.com/us/products/1471772>



Outdoor housing, color: light gray, dimensions: 8" x 6" x 4", incl. corner inlays, cover plugs, screws, cover: transparent, plastic latch, material: PC UV-stabilized

## Accessories

# OCS POLEFIX 0806 - Mounting material



1476923

<https://www.phoenixcontact.com/us/products/1476923>

## SF-SLIC 1,6X10-175 - Screwdriver

1212555

<https://www.phoenixcontact.com/us/products/1212555>



Screwdriver, slot-headed, with impact cap, with hexagon wrench aid for open-end wrench and ring wrench, size: 1.6 x 10 x 175 mm, 2-component grip

---

## SF-SLIC 1,2X7,0-125 - Screwdriver

1212554

<https://www.phoenixcontact.com/us/products/1212554>



Screwdriver, slot-headed, with impact cap, with hexagon wrench aid for open-end wrench and ring wrench, size: 1.2 x 7.0 x 125 mm, 2-component grip, with non-slip grip

# OCS POLEFIX 0806 - Mounting material



1476923

<https://www.phoenixcontact.com/us/products/1476923>

## SF-SOCKET SET 47 - Tool set

1200292

<https://www.phoenixcontact.com/us/products/1200292>



**1/4" socket set**, 47-piece, 1/4" reversible ratchet, 48 teeth with fast locking system, 50 mm and 100 mm 1/4" extensions, 1/4" screwdriver handle, 150 mm 1/4" flexible extension, 1/4" Cardan joint, 1/4" T-handle  
2 x 1/4" bit adapter, 13 knurled 1/4" sockets, wrench size: 4 / 4.5 / 5 / 5.5 / 6 / 7 / 8 / 9 / 10 / 11 / 12 / 13 / 14 mm, 21 knurled socket bits: 6 x Torx<sup>®</sup> T10, T15, T20, T25, T30, T40, 6 x Hex 3, 4, 5, 6, 7, 8 mm, 3 x Phillips recess<sup>®</sup> PH1, PH2, PH3, 3 x Pozidriv<sup>®</sup> PZ1, PZ2, PZ3, 3 x slotted 4, 5.5, 7 mm, Allen wrench Hex 1.27, 1.5, 2, 2.5 mm, breakage and impact-resistant plastic case with metal fastening

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)