

FOC-PP-OS24-LCD12-OM1 - Distributor



1208056

<https://www.phoenixcontact.com/us/products/1208056>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor, design: Rail-mountable module, degree of protection: IP20, number of positions: 24, material: Metal, connection method: M17 circular connector, cable outlet: above and below, housing size: 1, color: gray, Ethernet

Product description

FDX-20 series DIN rail distributor for Plug and Play connection, equipped with 6x LC Quad couplings and 1x Q-ODC 24-pos. socket, socket attached on the underside (upon request, the socket can also be attached on the top). Housing (2-part) prepared for DIN rail mounting through the rear-side adapter (this can also be mounted on the side)

Your advantages

- Intuitive front-panel operation and clear control cabinet layout thanks to uniform design
- Flexible DIN rail mounting possible in six positioning directions
- Suitable for industrial applications
- Reduced installation time with plug-and-play
- Pin assignment straight in line in a link
- Continuously reliable data connection, thanks to extensively tested components
- Snap-on mounting on standard NS 35/7,5 or NS 35/15 DIN rails
- Transmission rate up to 1,000 Mbps

Commercial data

Item number	1208056
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB15
Product key	ABNHAC
GTIN	4063151275846
Weight per piece (including packing)	672.8 g
Weight per piece (excluding packing)	672.8 g
Customs tariff number	85367000
Country of origin	DE

1208056

<https://www.phoenixcontact.com/us/products/1208056>

Technical data

Product properties

Type	Rail-mountable module
Product type	Network distributor box
Sensor type	Ethernet
Number of positions	24
Connection profile	LC-Duplex
No. of conductors	24
Number of module slots	6
Number of slots	24
Protective cover	yes
Cable outlet	above and below

Electrical properties

Attenuation	≤ 0.6 dB
Transmission medium	FO

Connection data

Connection technology

Connection method	M17 circular connector
-------------------	------------------------

Dimensions

Width	40 mm
Height	130 mm
Depth	115 mm

Housing

Housing width	40 mm
---------------	-------

Mechanical characteristics

Ferrule diameter	1.25 mm
------------------	---------

Material specifications

Color	gray
Flammability rating according to UL 94	V0
Ferrule material	PPS
Housing surface material	Powder-coated, gray (metal housing)
Housing material	Metal

Cable/line

Cable type	Multimode fiberglass
Cable type	Fan out
External cable diameter	≤ 12 mm (of 6 mm)

1208056

<https://www.phoenixcontact.com/us/products/1208056>

	6 mm ... 12 mm
Individual wire diameter	2 mm

FO cable

Number of fibers	24
Fiber	GOF
Fiber type	Multimode fiberglass 62.5/125 µm
Transmission medium	FO

Characteristics

Attenuation	≤ 0.6 dB
-------------	----------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 55 °C

Mounting

Mounting type	DIN rail mounting
Assembly instructions	Option for flexible replugging of DIN rail adapter
Connection method	M17 circular connector

1208056

<https://www.phoenixcontact.com/us/products/1208056>

Classifications

ECLASS

ECLASS-11.0	19170113
ECLASS-12.0	19170113
ECLASS-13.0	19170113

ETIM

ETIM 9.0	EC002699
----------	----------

UNSPSC

UNSPSC 21.0	43223300
-------------	----------

1208056

<https://www.phoenixcontact.com/us/products/1208056>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

FOC-PP-OS24-LCD12-OM1 - Distributor



1208056

<https://www.phoenixcontact.com/us/products/1208056>

Accessories

FOC-TOOL-FERRULECLEANER-MT - FO accessories

1111534

<https://www.phoenixcontact.com/us/products/1111534>



Ferrule cleaner, for cleaning of MT inserts, can be used for approx. 500 cleaning cycles

FOC-OP24-OP24-GL03/10 - Connecting cable

1007606

<https://www.phoenixcontact.com/us/products/1007606>



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

FOC-PP-OS24-LCD12-OM1 - Distributor



1208056

<https://www.phoenixcontact.com/us/products/1208056>

FOC-OP24-OP24-GL03/20 - Connecting cable

1007629

<https://www.phoenixcontact.com/us/products/1007629>



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

FOC-OP24-OP24-GL03/30 - Connecting cable

1007632

<https://www.phoenixcontact.com/us/products/1007632>



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

FOC-PP-OS24-LCD12-OM1 - Distributor



1208056

<https://www.phoenixcontact.com/us/products/1208056>

FOC-OP24-OP24-GL03/40 - Connecting cable

1007803

<https://www.phoenixcontact.com/us/products/1007803>



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

FOC-OP24-OP24-GL03/50 - Connecting cable

1007602

<https://www.phoenixcontact.com/us/products/1007602>



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

FOC-PP-OS24-LCD12-OM1 - Distributor



1208056

<https://www.phoenixcontact.com/us/products/1208056>

FOC-OP24-OP24-GL03/100 - Connecting cable

1007809

<https://www.phoenixcontact.com/us/products/1007809>



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

FOC-OP24-OP24-GL03/160 - Connecting cable

1007640

<https://www.phoenixcontact.com/us/products/1007640>



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

FOC-PP-OS24-LCD12-OM1 - Distributor



1208056

<https://www.phoenixcontact.com/us/products/1208056>

FOC-OP24-OP24-GL03/200 - Connecting cable

1007641

<https://www.phoenixcontact.com/us/products/1007641>



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

FOC-FR19:1U-OS24-LCD12-OM1 - 19" mounting frame

1081342

<https://www.phoenixcontact.com/us/products/1081342>



Fiber optics distribution box, type: 19"-rack mount fiber optics distribution box, degree of protection: IP20, number of positions: 1*24, marking material: aluminum, color: gray

FOC-PP-OS24-LCD12-OM1 - Distributor



1208056

<https://www.phoenixcontact.com/us/products/1208056>

FOC-FR19:1U-2OS24-LCD24-OM1 - 19" mounting frame

1081340

<https://www.phoenixcontact.com/us/products/1081340>

Fiber optics distribution box, type: 19"-rack mount fiber optics distribution box, degree of protection: IP20, number of positions: 2*24, marking material: aluminum, color: gray




FOC-LC:PA-LC:PA-OM1:D01/0.5 - FO patch cable

1144197

<https://www.phoenixcontact.com/us/products/1144197>

Multi-mode OM1 duplex jumper, LC-LC, UPC polishing, length 0.5 m



FOC-PP-OS24-LCD12-OM1 - Distributor



1208056


<https://www.phoenixcontact.com/us/products/1208056>

FOC-LC:PA-LC:PA-OM1:D01/1 - FO patch cable

1146497

<https://www.phoenixcontact.com/us/products/1146497>

Multi-mode OM1 duplex jumper, LC-LC, UPC polishing, length 1 m




FOC-LC:PA-LC:PA-OM1:D01/2 - FO patch cable

1146505

<https://www.phoenixcontact.com/us/products/1146505>

Multi-mode OM1 duplex jumper, LC-LC, UPC polishing, length 2 m



FOC-PP-OS24-LCD12-OM1 - Distributor




1208056

<https://www.phoenixcontact.com/us/products/1208056>

FOC-LC:PA-LC:PA-OM1:D01/3 - FO patch cable

1111843

<https://www.phoenixcontact.com/us/products/1111843>




FO patch cable, degree of protection: IP20, cable length: 3 m, number of positions: 2, 40 Gbps, OM1

FOC-LC:PA-LC:PA-OM1:D01/5 - FO patch cable

1146514

<https://www.phoenixcontact.com/us/products/1146514>



Multi-mode OM1 duplex jumper, LC-LC, UPC polishing, length 5 m

FOC-PP-OS24-LCD12-OM1 - Distributor



1208056


<https://www.phoenixcontact.com/us/products/1208056>

FOC-LC:PA-LC:PA-OM1:D01/10 - FO patch cable

1146520

<https://www.phoenixcontact.com/us/products/1146520>

Multi-mode OM1 duplex jumper, LC-LC, UPC polishing, length 10 m



FOC-OP24-OP24-GL03/60 - Connecting cable

1007626

<https://www.phoenixcontact.com/us/products/1007626>

Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24



FOC-PP-OS24-LCD12-OM1 - Distributor



1208056

<https://www.phoenixcontact.com/us/products/1208056>

FOC-OP24-OP24-GL03/70 - Connecting cable

1007635

<https://www.phoenixcontact.com/us/products/1007635>



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

FOC-OP24-OP24-GL03/80 - Connecting cable

1007627

<https://www.phoenixcontact.com/us/products/1007627>



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

FOC-PP-OS24-LCD12-OM1 - Distributor



1208056

<https://www.phoenixcontact.com/us/products/1208056>

FOC-OP24-OP24-GL03/90 - Connecting cable

1007636

<https://www.phoenixcontact.com/us/products/1007636>



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

FOC-OP24-OP24-GL03/120 - Connecting cable

1007638

<https://www.phoenixcontact.com/us/products/1007638>



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

FOC-PP-OS24-LCD12-OM1 - Distributor



1208056

<https://www.phoenixcontact.com/us/products/1208056>

FOC-OP24-OP24-GL03/140 - Connecting cable

1007808

<https://www.phoenixcontact.com/us/products/1007808>



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

FOC-OP24-OP24-GL03/180 - Connecting cable

1007807

<https://www.phoenixcontact.com/us/products/1007807>



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 24

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com