

# PLD E 608-CA-MS/0,6/FS/UL - Power cable



2702307

<https://www.phoenixcontact.com/us/products/2702307>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power cable, 3-position, PVC, gray RAL 7001, Plug straight, coding: black, on Socket straight, coding: black, cable length: 0.6 m, with UL approval

## Product description

The cable serves to connect multiple 600 class PLD enclosure lights in series.

## Commercial data

Item number	2702307
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR08
Product key	DRL23Z
Catalog page	Page 500 (C-6-2019)
GTIN	4055626113326
Weight per piece (including packing)	95 g
Weight per piece (excluding packing)	95 g
Customs tariff number	85444290
Country of origin	DE

2702307

<https://www.phoenixcontact.com/us/products/2702307>

## Technical data

### Product properties

Product type	Power cable
Number of positions	3
Application	Enclosure lights
No. of cable outlets	1
Shielded	no

### Material specifications

Material for screw connection	not available
Outer sheath, material	PVC
Conductor material	Bare Cu litz wires

### Electrical properties

Nominal voltage $U_N$	250 V AC
Nominal current $I_N$	16 A

### Connector

#### Connection 1

Head design	Plug
Head cable outlet	straight
Coding	black

#### Connection 2

Head design	Socket
Head cable outlet	straight
Coding	black

### Cable/line

Cable length	0.6 m
--------------	-------

#### H05VV-F3G [PVC]

Number of positions	3
Shielded	no
Cable type	H05VV-F3G [PVC]
AWG signal line	16
Wire diameter incl. insulation	2.7 mm
External cable diameter	7.8 mm
Outer sheath, material	PVC
External sheath, color	gray RAL 7001
Conductor material	Bare Cu litz wires
Material wire insulation	PVC TI2
Smallest bending radius, fixed installation	40 mm

# PLD E 608-CA-MS/0,6/FS/UL - Power cable



2702307

<https://www.phoenixcontact.com/us/products/2702307>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
	IP40 (plugged in)
Ambient temperature (operation)	-5 °C ... 40 °C

# PLD E 608-CA-MS/0,6/FS/UL - Power cable



2702307

<https://www.phoenixcontact.com/us/products/2702307>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702307>



**UL Recognized**

Approval ID: FILE E 118976

# PLD E 608-CA-MS/0,6/FS/UL - Power cable



2702307

<https://www.phoenixcontact.com/us/products/2702307>

## Classifications

### ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311

### ETIM

ETIM 8.0	EC001855
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# PLD E 608-CA-MS/0,6/FS/UL - Power cable



2702307

<https://www.phoenixcontact.com/us/products/2702307>

## Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

# PLD E 608-CA-MS/0,6/FS/UL - Power cable

2702307

<https://www.phoenixcontact.com/us/products/2702307>



## Accessories

### PLD E 608-CO-MS/FS/FR - T distributor

2702310

<https://www.phoenixcontact.com/us/products/2702310>



T-distributor with 2 sockets and one connector for series connection, black, 3-pos.

---

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)