

PRC COVER M - Protective cap



1409237

<https://www.phoenixcontact.com/us/products/1409237>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective cap, Range of articles: PRC 35, housing material: PPE, color: black, rated voltage: 1000. Suitable for connectors (MS)

Your advantages

- Reliable protection against environmental influences when not plugged in
- Ideal for indoor and outdoor use due to weatherproof materials
- Suitable for applications in atmospheres containing salt exposed to direct sunlight

Commercial data

Item number	1409237
Packing unit	1 pc
Minimum order quantity	50 pc
Sales key	AB03
Product key	ABL C ZC
Catalog page	Page 77 (NTK-2014)
GTIN	4046356867764
Weight per piece (including packing)	4.25 g
Weight per piece (excluding packing)	4.25 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Notes

General	Suitable for connectors (MS)
Safety note	<ul style="list-style-type: none">• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product. <p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p> <ul style="list-style-type: none">• Assembled products may not be manipulated or improperly opened.• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).• When using the product in direct connection with third-party manufacturers, the user is responsible.• For operating voltages > 50 V AC, conductive connector housings must be grounded• Ensure that the protective or functional ground has been properly connected.• VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector• Observe the corresponding technical data. You will find information:<ul style="list-style-type: none">o On the producto On the packing labelo In the supplied documentationo Online at phoenixcontact.com/products under the product• Only use tools recommended by Phoenix Contact• The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.• Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at phoenixcontact.com/products• Operate the connector only when it is fully plugged in.• Operate the connector only when it is fully plugged in and interlocked.• Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.

PRC COVER M - Protective cap



1409237

<https://www.phoenixcontact.com/us/products/1409237>

- Observe the minimum bending radius of the cable. Lay the cable without twisting it.
- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

Product properties

Product type	Installation connector
Product family	PRC 35

Insulation characteristics

Protection class	II
Degree of pollution	2

Electrical properties

Nominal voltage ATD	1000 (III/2) DIN VDE 60664-1
	600 V AC / DC (III/2) in accordance with UL 2238 / UL 2237
	500 V AC / DC (III/2) in accordance with IEC 61535, when mounted

Dimensions

Width	37.8 mm
Height	20.8 mm
Length	26.4 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP66 / IP68 (2m / 24h)
Degree of protection	IP66 / IP68 (2m / 24h)
	IP66 / IP68 (2 m / 24 h)
Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (assembly)	5 °C ... 85 °C

PRC COVER M - Protective cap



1409237

<https://www.phoenixcontact.com/us/products/1409237>

Classifications

ECLASS

ECLASS-11.0	27440109
ECLASS-12.0	27440109
ECLASS-13.0	27440109

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PRC COVER M - Protective cap



1409237

<https://www.phoenixcontact.com/us/products/1409237>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e No hazardous substances above threshold values
------------	---

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com