

WP-CTA POM 13,0 BK - Protective hose adapter



1422884

<https://www.phoenixcontact.com/us/products/1422884>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hose adapter, for corrugated hoses with a nominal size of 13 (10 x 13), corrugated in parallel

Commercial data

Item number	1422884
Packing unit	1 pc
Minimum order quantity	10 pc
Sales key	BF46
Product key	BF1ZVX
GTIN	4055626316567
Weight per piece (including packing)	1.622 g
Weight per piece (excluding packing)	1.622 g
Customs tariff number	39269097
Country of origin	CZ

WP-CTA POM 13,0 BK - Protective hose adapter



1422884

<https://www.phoenixcontact.com/us/products/1422884>

Technical data

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C
---------------------------------	------------------

Material specifications

Material	POM
----------	-----

Cable/line

External cable diameter ()	4 mm ... 7 mm
-----------------------------	---------------

Dimensions

Length	20 mm
--------	-------

WP-CTA POM 13,0 BK - Protective hose adapter



1422884

<https://www.phoenixcontact.com/us/products/1422884>

Classifications

ECLASS

ECLASS-11.0	27430308
ECLASS-12.0	27430308
ECLASS-13.0	27430308

ETIM

ETIM 9.0	EC001469
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

WP-CTA POM 13,0 BK - Protective hose adapter



1422884

<https://www.phoenixcontact.com/us/products/1422884>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

WP-CTA POM 13,0 BK - Protective hose adapter



1422884

<https://www.phoenixcontact.com/us/products/1422884>

Accessories

WP-PA HF 13,0 BK - Protective hose

3240681

<https://www.phoenixcontact.com/us/products/3240681>



Protective hose, material: PA 6, UV-resistant: yes, flexible, degree of protection: IP68, color: black, flammability rating in acc. with UL 94: V0, inner diameter: 10 mm, Total length: 50 m

WP-PA HF-HB 13,0 BK - Protective hose

3240839

<https://www.phoenixcontact.com/us/products/3240839>



Protective hose, material: PA 6, UV-resistant: yes, flexible, degree of protection: IP68, color: black, flammability rating in acc. with UL 94: HB, inner diameter: 10 mm, Total length: 50 m

WP-CTA POM 13,0 BK - Protective hose adapter

1422884

<https://www.phoenixcontact.com/us/products/1422884>



UNIFOX-C VDE - Combination pliers

1212202

<https://www.phoenixcontact.com/us/products/1212202>



Combination pliers, notched gripping surface, VDE 1000 V AC/1500 V DC tested, size: 180 mm

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com