

HS LCA-WH 10X5-L - Signal light



1474401

<https://www.phoenixcontact.com/us/products/1474401>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Signal light with litz wires, active, flexible



Commercial data

Item number	1474401
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC05
Product key	ACGABC
GTIN	4063151888183
Weight per piece (including packing)	5.7 g
Weight per piece (excluding packing)	3 g
Customs tariff number	90019000
Country of origin	TN

HS LCA-WH 10X5-L - Signal light



1474401

<https://www.phoenixcontact.com/us/products/1474401>

Technical data

Notes

General	The light guide is designed to be pressed into an H7-tolerated receptacle. Dry-install the LED display by pressing it in vertically. As an alternative, you can glue in the LED display, e.g., using LOCTITE 460.
General	Refer to the data sheet for the range in the download area.

Product properties

Product type	Light
Number of positions	1
Alignment	flexible
Type	active, flexible
Conductor type	Signal light with litz wires
Head form	Raised head
Number of indicators	1 (1 row x 1 column)

Dimensions

Diameter	10 mm (Aperture diameter)
	5 mm (Lens diameter)
Hole diameter	8 mm
Dimensions	(Cable ends)

Material specifications

Color Linse	transparent
Color Gehäuse	silver
Insulating material	PC

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP68
Ambient temperature (operation)	-20 °C ... 80 °C

Packaging specifications

Type of packaging	PE bag
-------------------	--------

HS LCA-WH 10X5-L - Signal light



1474401

<https://www.phoenixcontact.com/us/products/1474401>

Classifications

ECLASS

ECLASS-11.0	27110201
ECLASS-12.0	27110201
ECLASS-13.0	27110201

ETIM

ETIM 9.0	EC002750
----------	----------

HS LCA-WH 10X5-L - Signal light

1474401

<https://www.phoenixcontact.com/us/products/1474401>

Accessories

SZS 0,4X2,0 - Screwdriver

1205202

<https://www.phoenixcontact.com/us/products/1205202>



Micro screwdriver, bladed, size: 0.4 x 2.0 x 60 mm, 2-component grip, with non-slip grip and twist cap

PTSM 0,5/ 2-PL-2,5 WH - Printed-circuit board connector

1709457

<https://www.phoenixcontact.com/us/products/1709457>



PCB connector, nominal cross section: 0.5 mm², color: white, nominal current: 6 A, rated voltage (III/2): 160 V, contact surface: Tin, contact connection type: Socket, number of potentials: 2, number of rows: 1, number of positions: 2, number of connections: 2, product range: PTSM 0,5/...-PL WH, pitch: 2.5 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON PTSM, locking: Snap-in locking, mounting: Self-locking flange, type of packaging: packed in cardboard

HS LCA-WH 10X5-L - Signal light

1474401

<https://www.phoenixcontact.com/us/products/1474401>



PTSM 0,5/ 2-PL-2,5 BK - Printed-circuit board connector

1709442

<https://www.phoenixcontact.com/us/products/1709442>



PCB connector, nominal cross section: 0.5 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact surface: Tin, contact connection type: Socket, number of potentials: 2, number of rows: 1, number of positions: 2, number of connections: 2, product range: PTSM 0,5/...-PL, pitch: 2.5 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON PTSM, locking: Snap-in locking, mounting: Self-locking flange, type of packaging: packed in cardboard

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com