

EM-DUO 120/15/GFI/V/H - Socket



5604775

<https://www.phoenixcontact.com/us/products/5604775>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Rail-mounted dual socket with integrated fault current circuit breaker. For vertical or horizontal mounting on 35 mm DIN rail per EN 60715. Housing color: ivory. Receptacle style: USA. Connection type: screw.

Commercial data

Item number	5604775
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE76
Product key	BE7613
GTIN	4046356687577
Weight per piece (including packing)	33.33 g
Weight per piece (excluding packing)	33.33 g
Customs tariff number	85366990
Country of origin	US

Technical data

Notes

Trade restriction

CE note	The products are offered exclusively for export outside the EU and the European Economic Area.
---------	--

Product properties

Product type	Socket
For country-specific use in	USA
	Canada
	Japan
	Mexico
	Saudi Arabia
	Taiwan
Venezuela	

Electrical properties

Nominal voltage U_N	125 V AC
Nominal current I_N	15 A

Material specifications

Color	ivory
Insulating material	PVC 94 V0

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C

Standards and regulations

Standards

Standards/regulations	UL 508
	CSA 22.2

Mounting

Connection method	Screw connection
-------------------	------------------

EM-DUO 120/15/GFI/V/H - Socket





5604775

<https://www.phoenixcontact.com/us/products/5604775>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/5604775>

 UL Listed Approval ID: FILE E 238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	15 A	-	30 - 10

 cUL Listed Approval ID: FILE E 238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	15 A	30 - 10	-

cULus Listed				
---------------------	--	--	--	--

EM-DUO 120/15/GFI/V/H - Socket



5604775

<https://www.phoenixcontact.com/us/products/5604775>

Classifications

ECLASS

ECLASS-11.0	27142305
ECLASS-12.0	27142305
ECLASS-13.0	27142305

ETIM

ETIM 8.0	EC001663
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

EM-DUO 120/15/GFI/V/H - Socket



5604775

<https://www.phoenixcontact.com/us/products/5604775>

Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com