

WP 6121-WXPS - Web panel



1290802

<https://www.phoenixcontact.com/us/products/1290802>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IP66 Touch panel with 12.1-inch widescreen (16:9) XGA, PCAP display, Software: Qt Browser



Your advantages

- Easy startup – just enter the IP and URL
- Flexible, thanks to open web standard and free choice of web server and visualization software
- No security updates are required for JAVA or Flash plug-ins thanks to HTML5
- Ideal for use with PLCnext Engineer or CODESYS
- Embedded Linux operating system
- Visualization of self-programmed JavaScript applications possible

Commercial data

Item number	1290802
Packing unit	1 pc
Sales key	DR17
Product key	DRCADF
GTIN	4063151522650
Weight per piece (including packing)	2,260 g
Weight per piece (excluding packing)	2,100 g
Country of origin	TW

Technical data

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm® Cortex®-A53, 1.6 GHz
Operating system	Yocto/Linux
Data storage system	Flash eMMC, 8 GB
Slots	1x microSD

Display

Display type	30.7 cm/12.1" TFT
Screen resolution	1280 x 800 Pixel(s) (WXGA)
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	400 cd/m², typical (adjustable)
MTBF	50000 h
Color spectrum	16.7 million colors
Reading angle left	88 °
Reading angle right	88 °
Reading angle top	88 °
Reading angle bottom	88 °

Software

User software	QT browser
---------------	------------

System requirements

Runtime system	Qt Browser
----------------	------------

Interfaces

Interfaces	2x USB Host 2.0, 1x USB Type C 3.0
	1x COM (RS-232/422/485)
Optional interfaces	Without optional interface
Network	1x Ethernet (10/100/1000 Mbps), RJ45
Bus system	without

System properties

User software	QT browser
---------------	------------

System requirements

Runtime system	Qt Browser
----------------	------------

Electrical properties

Supply

WP 6121-WXPS - Web panel



1290802

<https://www.phoenixcontact.com/us/products/1290802>

Supply voltage	24 V DC
Supply voltage range	18 V ... 32 V
Power supply unit	24 V DC \pm 20 %

Real-time clock

Realtime clock	Integrated (battery backup)
----------------	-----------------------------

Mounting

Mounting type	Front mounting
---------------	----------------

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Aluminum cast alloy, powder-coated

Connection data

Connection method	Screw connection
Conductor cross section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12
Stripping length	7 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66 (front), IP20 (back)
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 85 % (non-condensing)
Vibration (operation)	1g

Dimensions

External dimensions

Width / Height / Depth	302 mm / 229 mm / 51 mm (Dimensions of the front plate)
------------------------	---

Installation dimensions

Width / Height / Installation depth	292 mm / 219 mm / (Installation cutout)
-------------------------------------	---

WP 6121-WXPS - Web panel



1290802

<https://www.phoenixcontact.com/us/products/1290802>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1290802>



EAC

Approval ID: RU C-DE.A*08.B01708



IECEE CB Scheme

Approval ID: US-39088-UL



UL Listed

Approval ID: FILE E 238705



cUL Listed

Approval ID: FILE E 238705

cULus Listed

1290802

<https://www.phoenixcontact.com/us/products/1290802>

Classifications

ECLASS

ECLASS-11.0	27330201
ECLASS-12.0	27330201
ECLASS-13.0	27330201

ETIM

ETIM 9.0	EC001412
----------	----------

UNSPSC

UNSPSC 21.0	43211900
-------------	----------

WP 6121-WXPS - Web panel

1290802

<https://www.phoenixcontact.com/us/products/1290802>



Environmental product compliance

REACH SVHC

Lead 7439-92-1

WP 6121-WXPS - Web panel

1290802

<https://www.phoenixcontact.com/us/products/1290802>



Accessories

TP6/WP6/VL3 MOUNTING HW (2PCS) - Panel-mount flange

1289537

<https://www.phoenixcontact.com/us/products/1289537>



Mounting kit includes two retaining clips

TP/WP 6000 RTC BATTERY KIT - Battery

1289761

<https://www.phoenixcontact.com/us/products/1289761>



Replacement battery for TP 6000 and WP 6000 panels, and VL3 BPC/PPC/UPC.

WP 6121-WXPS - Web panel

1290802

<https://www.phoenixcontact.com/us/products/1290802>



MSTB 2,5/ 3-STF-5,08 - PCB connector

1777992

<https://www.phoenixcontact.com/us/products/1777992>



PCB connector, nominal cross section: 2.5 mm², color: green, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Tin, contact connection type: Socket, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: MSTB 2,5/...-STF, pitch: 5.08 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON MSTB 2,5, locking: Screw locking mechanism, mounting: Screw flange, type of packaging: packed in cardboard

MICROSDHC-16GB - Memory

1154696

<https://www.phoenixcontact.com/us/products/1154696>



Industrial grade 16 GB MicroSDHC 3DTLC

WP 6121-WXPS - Web panel

1290802

<https://www.phoenixcontact.com/us/products/1290802>



MICROSDHC-32GB - Memory

1154699

<https://www.phoenixcontact.com/us/products/1154699>



Industrial grade 32 GB MicroSDHC 3DTLC

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com