

PHT22-FR-WH/PT10 - Button



1108029

<https://www.phoenixcontact.com/gb/products/1108029>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Flat button, 22 mm, circular, white, automatic reset, including a button head, module holder, and a N/O contact module using push-in connection technology

Your advantages

- 22 mm push button set with push-in action

Commercial data

Item number	1108029
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE6122
Product key	BE6122
GTIN	4063151011321
Weight per piece (including packing)	37.5 g
Weight per piece (excluding packing)	37.5 g
Country of origin	CN

Technical data

Product properties

Product type	Actuator
Insulation characteristics	
Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	5 W

Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.5 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.5 mm ² ... 1.5 mm ²
Conductor cross-section, flexible [AWG]	20 ... 16 (converted acc. to IEC)
2 conductors with same cross section, rigid	0.5 mm ² ... 2.5 mm ²
2 conductors with the same cross-section AWG rigid	20 ... 16 (converted acc. to IEC)
2 conductors with same cross section, flexible	0.5 mm ² ... 1.5 mm ²
2 conductors with the same cross-section AWG flexible	20 ... 16 (converted acc. to IEC)
2 conductors with the same cross section, flexible, with ferrule with plastic sleeve	0.5 mm ² ... 2.5 mm ²
Thermal continuous current I_{th}	10 A

Dimensions

Width	30 mm
Height	46 mm

Installation dimensions

Installation depth	47.9 mm
--------------------	---------

Material specifications

Color	white
-------	-------

Environmental and real-life conditions

Degree of protection (IP code)

Degree of protection	IP66
----------------------	------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 85 °C
Permissible humidity (operation)	≤ 95 % ((room temperature 25°C) no condensation)

PHT22-FR-WH/PT10 - Button



1108029

<https://www.phoenixcontact.com/gb/products/1108029>

Standards and regulations

Standards/specifications	IEC 60947-5-1
	GB 14048.5
	UL 60947-5-1

Mounting

Mounting type	Panel mount
---------------	-------------

PHT22-FR-WH/PT10 - Button


1108029

<https://www.phoenixcontact.com/gb/products/1108029>



Drawings


Circuit diagram



1108029

<https://www.phoenixcontact.com/gb/products/1108029>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1108029>



cULus Listed

Approval ID: E172140



CCC

Approval ID: 2024010305697836

Functional Safety

Approval ID: R CN21G3UE 001

PHT22-FR-WH/PT10 - Button



1108029

<https://www.phoenixcontact.com/gb/products/1108029>

Classifications

ECLASS

ECLASS-15.0	27371228
ECLASS-13.0	27371228

ETIM

ETIM 10.0	EC001028
-----------	----------

1108029

<https://www.phoenixcontact.com/gb/products/1108029>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk