

PHT22-FRD-YE/PT10/YE - Button

1108280

<https://www.phoenixcontact.com/gb/products/1108280>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Illuminated flat button, 22 mm, circular, yellow, automatic reset, including a button head, module holder, a N/O contact module using push-in connection technology and a LED module

Your advantages

- 22 mm illuminated button set with Push-in connection
- Self-retaining (latching) – ideal for switching functions
- Depending on the set variant, incl. contact module(s) (N/O / N/C, 1- or 2-way) + 1 LED module – flexible in use
- With integrated lighting option for clear status display
- Quick mounting in the control cabinet/control panel

Commercial data

Item number	1108280
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE6122
Product key	BE6122
GTIN	4063151012076
Weight per piece (including packing)	47.6 g
Weight per piece (excluding packing)	43.7 g
Country of origin	CN

Technical data

Product properties

Product type	Actuator
--------------	----------

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	5 W

Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.5 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.5 mm ² ... 1.5 mm ²
Conductor cross-section, flexible [AWG]	20 ... 16 (converted acc. to IEC)
2 conductors with same cross section, rigid	0.5 mm ² ... 2.5 mm ²
2 conductors with the same cross-section AWG rigid	20 ... 16 (converted acc. to IEC)
2 conductors with same cross section, flexible	0.5 mm ² ... 1.5 mm ²
2 conductors with the same cross-section AWG flexible	20 ... 16 (converted acc. to IEC)
Thermal continuous current I_{th}	10 A

Dimensions

Width	30 mm
Height	46 mm

Installation dimensions

Installation depth	47.9 mm
--------------------	---------

Material specifications

Color	yellow
-------	--------

Environmental and real-life conditions

Degree of protection (IP code)

Degree of protection	IP66
----------------------	------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 85 °C
Permissible humidity (operation)	≤ 95 % ((room temperature 25°C) no condensation)

Standards and regulations

PHT22-FRD-YE/PT10/YE - Button



1108280

<https://www.phoenixcontact.com/gb/products/1108280>

Standards/specifications	IEC 60947-5-1
	GB 14048.5
	UL 60947-5-1

Mounting

Mounting type	Panel mount
---------------	-------------

PHT22-FRD-YE/PT10/YE - Button


1108280

<https://www.phoenixcontact.com/gb/products/1108280>



Drawings

Circuit diagram



1108280

<https://www.phoenixcontact.com/gb/products/1108280>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1108280>



cULus Listed

Approval ID: E172140



CCC

Approval ID: 2024010305697836

Functional Safety

Approval ID: R CN21G3UE 001

PHT22-FRD-YE/PT10/YE - Button



1108280

<https://www.phoenixcontact.com/gb/products/1108280>

Classifications

ECLASS

ECLASS-13.0	27371228
ECLASS-15.0	27371228

ETIM

ETIM 10.0	EC001028
-----------	----------

1108280

<https://www.phoenixcontact.com/gb/products/1108280>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk