

PHT22-PL-YE - LED light

1109039

<https://www.phoenixcontact.com/gb/products/1109039>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Indicator, 22 mm, round, yellow, LED integrated, AC/DC 24 ... 240 V, PT Push-in connection



Your advantages

- 22 mm indicator light with push-in mounting
- Large voltage range 24 ... 240 V AC/DC
- High visibility thanks to bright, uniform light
- Available in different colors
- Robust, touch-proof design for industrial applications

Commercial data

Item number	1109039
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE6122
Product key	BE6122
GTIN	4063151018979
Weight per piece (including packing)	18.8 g
Weight per piece (excluding packing)	16.5 g
Customs tariff number	85318070
Country of origin	CN

PHT22-PL-YE - LED light



1109039

<https://www.phoenixcontact.com/gb/products/1109039>

Technical data

Product properties

Product type	LED display
--------------	-------------

Insulation characteristics

Degree of pollution	3
---------------------	---

Electrical properties

Rated surge voltage	4 kV
---------------------	------

Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.5 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.5 mm ² ... 1.5 mm ²
Conductor cross-section, flexible [AWG]	20 ... 16 (converted acc. to IEC)
2 conductors with same cross section, rigid	0.5 mm ² ... 2.5 mm ²
2 conductors with the same cross-section AWG rigid	20 ... 16 (converted acc. to IEC)
2 conductors with same cross section, flexible	0.5 mm ² ... 1.5 mm ²
2 conductors with the same cross-section AWG flexible	20 ... 16 (converted acc. to IEC)
2 conductors with the same cross section, flexible, with ferrule with plastic sleeve	0.5 mm ² ... 1.5 mm ²
Nominal current	25 mA (green)

Dimensions

Width	30 mm
Height	30 mm

Installation dimensions

Installation depth	28.2 mm
--------------------	---------

Material specifications

Color	yellow
-------	--------

Environmental and real-life conditions

Degree of protection (IP code)

Degree of protection	IP66
----------------------	------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 85 °C
Permissible humidity (operation)	≤ 95 % ((room temperature 25°C) no condensation)

Standards and regulations

PHT22-PL-YE - LED light



1109039

<https://www.phoenixcontact.com/gb/products/1109039>

Standards/specifications	IEC 60947-5-1
	GB 14048.5
	UL 60947-5-1

Mounting

Mounting type	Panel mount
---------------	-------------

PHT22-PL-YE - LED light


1109039

<https://www.phoenixcontact.com/gb/products/1109039>



Drawings

Circuit diagram



1 LED

PHT22-PL-YE - LED light



1109039

<https://www.phoenixcontact.com/gb/products/1109039>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1109039>



cULus Listed

Approval ID: E172140



CCC

Approval ID: 2024010305697836



CCC

Approval ID: 2025010305806583

Functional Safety

Approval ID: R CN21G3UE 001

PHT22-PL-YE - LED light

1109039

<https://www.phoenixcontact.com/gb/products/1109039>



Classifications

ECLASS

ECLASS-13.0	27371302
ECLASS-15.0	27371302

ETIM

ETIM 10.0	EC000041
-----------	----------

PHT22-PL-YE - LED light



1109039

<https://www.phoenixcontact.com/gb/products/1109039>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk