

UM122-PROFIL GN L 11,2CM - Profile



2201400

<https://www.phoenixcontact.com/gb/products/2201400>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Latching with side elements, latching with foot element, Basic profile, profile width (internal): 122 mm, profile width (external): 127.5 mm, length: 112 mm



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2201400 |
| Packing unit | 1 pc |
| Minimum order quantity | 100 pc |
| Note | Made to order (non-returnable) |
| Sales key | ACHDBA |
| Product key | ACHDBA |
| GTIN | 4046356793759 |
| Weight per piece (including packing) | 57.2 g |
| Weight per piece (excluding packing) | 57.2 g |
| Customs tariff number | 39162000 |
| Country of origin | DE |

UM122-PROFIL GN L 11,2CM - Profile



2201400

<https://www.phoenixcontact.com/gb/products/2201400>

Technical data

Product properties

| | |
|------------------------------|------------------------------|
| Product type | Component housing lower part |
| Housing type | Press-drawn section housings |
| Housing type | Extruded profile housings |
| Housing series | UM |
| Product family | UM122 |
| Ventilation openings present | no |

Dimensions

| | |
|--------|--------|
| Length | 112 mm |
|--------|--------|

External dimensions

| | |
|--------------------------|----------|
| Profile width (external) | 127.5 mm |
|--------------------------|----------|

Internal dimensions

| | |
|--------------------------|--------|
| Profile width (internal) | 122 mm |
|--------------------------|--------|

Material specifications

| | |
|------------------|------------------|
| Color (Profile) | green (RAL 6021) |
| Material Profile | PVC |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

Mounting

| | |
|---------------|---|
| Mounting type | Latching with side elements, latching with foot element |
|---------------|---|

UM122-PROFIL GN L 11,2CM - Profile



2201400

<https://www.phoenixcontact.com/gb/products/2201400>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190601 |
| ECLASS-15.0 | 27190601 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UM122-PROFIL GN L 11,2CM - Profile



2201400

<https://www.phoenixcontact.com/gb/products/2201400>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.147 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk