

SB 4-8-T - Bridge bar

3026379

<https://www.phoenixcontact.com/gb/products/3026379>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bridge bar, pitch: 8.2 mm, number of positions: 4, color: orange



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3026379 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE1Z2X |
| Product key | BE1Z2X |
| GTIN | 4017918351236 |
| Weight per piece (including packing) | 7.565 g |
| Weight per piece (excluding packing) | 7.42 g |
| Customs tariff number | 85369095 |
| Country of origin | PL |

SB 4-8-T - Bridge bar



3026379

<https://www.phoenixcontact.com/gb/products/3026379>

Technical data

Product properties

| | |
|---------------------|------------|
| Product type | Bridge bar |
| Number of positions | 4 |
| Pitch | 8.2 mm |
| Potentials | 1 |

Dimensions

| | |
|--------|---------|
| Width | 31.7 mm |
| Height | 15.6 mm |
| Depth | 15.6 mm |
| Pitch | 8.2 mm |

Material specifications

| | |
|---------------------|-------------------|
| Color | orange (RAL 2003) |
| Material | Copper |
| Insulating material | PA |

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -60 °C ... 105 °C |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Mounting

| | |
|---------------|------------------|
| Mounting type | Plug-in mounting |
|---------------|------------------|

SB 4-8-T - Bridge bar



3026379

<https://www.phoenixcontact.com/gb/products/3026379>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250303 |
| ECLASS-15.0 | 27250303 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000489 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SB 4-8-T - Bridge bar



3026379

<https://www.phoenixcontact.com/gb/products/3026379>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.069 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk