

WP-BASE C PA HF 10,0 BK - Hose holder with cover



3240958

<https://www.phoenixcontact.com/gb/products/3240958>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Hose holder with cover, material: PA, color: black, flammability rating in acc. with UL 94: V2

Commercial data

Item number	3240958
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AF7DSA
Product key	AF7DSA
GTIN	4046356710657
Weight per piece (including packing)	3.912 g
Weight per piece (excluding packing)	3.878 g
Customs tariff number	39174000
Country of origin	DE

WP-BASE C PA HF 10,0 BK - Hose holder with cover



3240958

<https://www.phoenixcontact.com/gb/products/3240958>

Technical data

Product properties

Product type	Mounting material
--------------	-------------------

Dimensions

Diameter	10 mm
Hole diameter	5.5 mm

Material specifications

Material	PA
Flammability rating according to UL 94	V2
Components	halogen-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

Mounting

Mounting type	Screw mounting
---------------	----------------

WP-BASE C PA HF 10,0 BK - Hose holder with cover



3240958

<https://www.phoenixcontact.com/gb/products/3240958>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3240958>



UL Recognized
Approval ID: E86359

WP-BASE C PA HF 10,0 BK - Hose holder with cover



3240958

<https://www.phoenixcontact.com/gb/products/3240958>

Classifications

ECLASS

ECLASS-15.0	27430315
ECLASS-13.0	27430315

ETIM

ETIM 10.0	EC000799
-----------	----------

UNSPSC

UNSPSC 21.0	31162900
-------------	----------

WP-BASE C PA HF 10,0 BK - Hose holder with cover



3240958

<https://www.phoenixcontact.com/gb/products/3240958>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.34 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk