

THERMOMARK CARD - Thermal transfer printer



5146464

<https://www.phoenixcontact.com/gb/products/5146464>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Thermal transfer printer for cards



Product description

The THERMOMARK CARD prints marking materials in card format for terminal marking, wire and cable marking, and equipment and plant marking to an incredibly high quality.

Your advantages

- Maintenance-free operation with proven thermal transfer printer technology
- High-quality, fast labeling. Printing time for one UniCard: just 8 seconds.
- Easy operating concept based on user-friendly touch screen entry
- Easy to control with the PROJECT COMPLETE software

Commercial data

Item number	5146464
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BG1221
Product key	BG1221
GTIN	4046356528795
Weight per piece (including packing)	9,820 g
Weight per piece (excluding packing)	9,200 g
Country of origin	DE

Technical data

Product properties

Product type	Marking system
--------------	----------------

Marking

Identification technology	Thermotransfer
---------------------------	----------------

Device properties

Print width	104 mm
Print resolution	300 dpi
Operating system	MS Windows Vista, MS Windows 7 (32/64-bit), MS Windows 8 (32/64-bit), MS Windows 8.1 (32/64-bit), MS Windows 10 (32/64-bit), Server 2008, Server 2008 R2, Server 2012, Server 2012 R2

Electrical properties

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	---

Dimensions

Width	254 mm
Height	194 mm
Length	325 mm

Material specifications

Color	gray
-------	------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 35 °C
Permissible humidity (operation)	10 % ... 80 %

5146464

<https://www.phoenixcontact.com/gb/products/5146464>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/5146464>



IECEE CB Scheme

Approval ID: DK-5443



UL Listed

Approval ID: E140403



cUL Listed

Approval ID: E140403



KC

Approval ID: KCC-REI-PCK-FL514646

THERMOMARK CARD - Thermal transfer printer



5146464

<https://www.phoenixcontact.com/gb/products/5146464>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk