

D-MPT 2,5-L - End cover

1075386

<https://www.phoenixcontact.com/pc/products/1075386>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, depth: 27 mm, height: 36 mm, color: gray



Commercial data

Item number	1075386
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	BE2Z1X
GTIN	4055626779737
Weight per piece (including packing)	1.626 g
Weight per piece (excluding packing)	1.62 g
Customs tariff number	85389099
Country of origin	PL

D-MPT 2,5-L - End cover



1075386

<https://www.phoenixcontact.com/pc/products/1075386>

Technical data

Product properties

Product type	End cover
--------------	-----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Dimensions

End cover width	3.2 mm
Height	36 mm
Depth	27 mm


D-MPT 2,5-L - End cover

1075386

<https://www.phoenixcontact.com/pc/products/1075386>

Drawings

Schematic diagram




D-MPT 2,5-L - End cover

1075386

<https://www.phoenixcontact.com/pc/products/1075386>



Schematic diagram




D-MPT 2,5-L - End cover

1075386

<https://www.phoenixcontact.com/pc/products/1075386>

Schematic diagram



D-MPT 2,5-L - End cover

1075386

<https://www.phoenixcontact.com/pc/products/1075386>



Classifications

ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

ETIM

ETIM 10.0	EC000886
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

D-MPT 2,5-L - End cover

1075386

<https://www.phoenixcontact.com/pc/products/1075386>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.016 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com