

RCK-TWUM/BL12/10,0PUR-UX - Master cable



1260755

<https://www.phoenixcontact.com/pc/products/1260755>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Master cable, application: Sensor/actuator box, number of positions: 12, slot assignment: single, status display: no; master cable connection: M23 plug connection, PUR/PVC, cable length: 10 m, shielding: no, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %). This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1260755
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABRDCB
GTIN	4063151414559
Weight per piece (including packing)	1,162.3 g
Weight per piece (excluding packing)	1,130.444 g
Customs tariff number	85444290
Country of origin	DE

1260755

<https://www.phoenixcontact.com/pc/products/1260755>

Technical data

Notes

Notes on operation	The master cable is earmarked for use on the sensor/actuator boxes with an M23 plug-in connection.
--------------------	--

Product properties

Product type	Master cable, assembled
Application	Sensor/actuator box
Number of positions	12

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC

Connection data

Connection method	Fixed connection
-------------------	------------------

Signaling

Status display present	no
------------------------	----

Material specifications

Material Housing	PUR
Material of contact, master cable side	CU alloy
Material of the contact carrier on the master cable side	PA
Material of contact surface, master cable side	gold-plated

Connector

Connection 1

Head design	Socket
Head cable outlet	angled
Head thread type	M23

Connection 2

Head design	free cable end
-------------	----------------

Cable/line


Cable length	10 m
--------------	------

PUR/PVC black [PUR]

RCK-TWUM/BL12/10,0PUR-UX - Master cable

1260755

<https://www.phoenixcontact.com/pc/products/1260755>

Dimensional drawing	
Cable weight	107.4 kg/km
UL AWM Style	20549 (80°C/300 V)
Number of positions	11
Shielded	no
Cable type	PUR/PVC black [PUR]
Conductor structure signal line	19x 0.15 mm
AWG signal line	22
Conductor structure, voltage supply	42x 0.15 mm
AWG power supply	18
Conductor cross-section	8x 0.34 mm ² (Signal line) 3x 0.75 mm ² (power line)
Wire diameter incl. insulation	1.3 mm ±0.1 mm (Signal line) 1.8 mm ±0.1 mm (power line)
External cable diameter	8.50 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, green/yellow, white, green, yellow, gray, pink, red, black, violet
Inner sheath thickness	≥ 0.15 mm
Thickness, outer sheath	≥ 0.38 mm
Overall twist	Wires twisted in layers
Max. conductor resistance	≤ 53 Ω/km (Signal line) ≤ 26 Ω/km (power line)
Insulation resistance	≥ 5 MΩ*km
Nominal voltage, cable	300 V AC
Test voltage Core/Core	2000 V (50 Hz, 5 min.)
Minimum bending radius, fixed installation	7.5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	64 mm
Smallest bending radius, movable installation	85 mm
Dynamic load capacity (bending)	Max. bending cycles: 1500000, Bending radius: 10 x D, Traversing path: 2 m, Traversing rate: 2 m/s
Flame resistance	DIN EN 50265
Resistance to oil	according to VDE 0472 Part 803

RCK-TWUM/BL12/10,0PUR-UX - Master cable



1260755

<https://www.phoenixcontact.com/pc/products/1260755>

Other resistance	Highly resistant to acids, alkaline solutions and solvents
Special properties	Silicone-free
Ambient temperature (operation)	-40 °C ... 90 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-40 °C ... 125 °C (Plug / socket)

Drawings

Schematic diagram



Pin assignment M23 socket, 12-pos., female side view

RCK-TWUM/BL12/10,0PUR-UX - Master cable



1260755

<https://www.phoenixcontact.com/pc/products/1260755>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/pc/products/1260755>



EAC

Approval ID: 19060508

1260755

<https://www.phoenixcontact.com/pc/products/1260755>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

RCK-TWUM/BL12/10,0PUR-UX - Master cable



1260755

<https://www.phoenixcontact.com/pc/products/1260755>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com