



| | | | | | | | | | | | | | | | | | | | | | | | |
|---------------|---|------------|--------|-----|-----|-------|-------|-------|--------|-------|-------|-------|-----|-----|-----|-----|---|--|--|------------------------|---------|--------------|--|
| -X371P | A14/2 3-stufiger Frequenzlastabwurf (AFE) | Stiftlänge | lang | | | | | | | | | | X | X | X | X | X | | | PRÜFSTECKER | 3069474 | FTP-2/A14 | |
| | | | mittel | | | | | | | | | | | | | | | | | | | | |
| | | | kurz | X | X | X | X | X | X | X | | | | | | | | | | | | | |
| | | Anschluss | 1b | 2b | 3b | 4b | 5b | 6b | 7b | 8b | 9b | 10b | 11b | 12b | 13b | 14b | | | | | | | |
| | Prüf-buchse | (X) | | (X) | | (X) | | (X) | | (X) | | (X) | | (X) | | | | | | PRÜFSTECKLEISTE | 3069439 | PTWE 6-2/A14 | |
| | Brücke | quer | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | | | | | | | | | |
| | | quer | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | | | | | | | | | |
| | Prüf-buchse | (X) | | (X) | | (X) | | (X) | | (X) | | (X) | | (X) | | | | | | | | | |
| | Anschluss | 1a | 2a | 3a | 4a | 5a | 6a | 7a | 8a | 9a | 10a | 11a | 12a | 13a | 14a | | | | | | | | |
| | Anschluss | 1b | 2b | 3b | 4b | 5b | 6b | 7b | 8b | 9b | 10b | 11b | 12b | 13b | 14b | | | | | | | | |
| | Brücke | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | | | | | | | | |
| | Brücke | X | | | | | | | | | | | | | | | | | | | | | |
| | Brücke | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | | | | | | | | |
| | Anschluss | 1a | 2a | 3a | 4a | 5a | 6a | 7a | 8a | 9a | 10a | 11a | 12a | 13a | 14a | | | | | | | | |
| | Anschluss-Bezeichnung | UN | UL1 | UL2 | UL3 | Anr 1 | Anr 2 | Anr 3 | Signal | L+A 1 | L+A 2 | L+A 3 | L-A | L+ | L- | | | | | | | | |

Signal

| | | |
|-------|--------------------|---------------------------|
| | Datum letzte Aend. | 05.06.2014 |
| | Letzter Bearbeiter | Hong-Phat Le |
| | Erstelldatum | 02.04.2014 |
| Index | Rev. Bezeichnung | Ersteller Hong-Phat Le |



3-stufiger Frequenzlastabwurf (AFE)
Anschaltungsbeispiel

| | | |
|----------------|----------------|--------------|
| Projektnummer: | &EFA = | = |
| Anmerkungen: | VARIANTE A14/2 | + A14 / 2 |
| | | Blatt von 56 |