



-X312P	Überstromrichtungszeitschutz wandlerstrombetätigt	B14/2	Stiftlänge	lang									X	X	X	X	X	X	PRÜFSTECKER	3069475	FTP-2/B14			
			Stiftlänge	mittel																				
			Stiftlänge	kurz	X	X	X	X	X	X	X													
			Anschluss	1b	2b	3b	4b	5b	6b	7b	8b	9b	10b	11b	12b	13b	14b							
			Prüfbuchse	(X)		(X)		(X)		(X)		(X)		(X)		(X)								
			Brücke	quer	○	○	○	○	○	○	○	○	○	○	○	○	○							
				längs	○	○	○	○	○	○	○	○	○	○	○	○	○							
				quer	○	○	○	○	○	○	○	○	○	○	○	○	○							
			Prüfbuchse	(X)		(X)		(X)		(X)		(X)		(X)		(X)								
			Anschluss	1a	2a	3a	4a	5a	6a	7a	8a	9a	10a	11a	12a	13a	14a							
			Brücke	quer	○	○	○	○	○	○	○	○	○	○	○	○	○							
				längs	○	○	○	○	○	○	○	○	○	○	○	○	○							
				quer	○	○	○	○	○	○	○	○	○	○	○	○	○							
			Anschluss	1a	2a	3a	4a	5a	6a	7a	8a	9a	10a	11a	12a	13a	14a							
Anschluss-Bezeichnung	IN	IL1	IL2	IL3	UN	UL1	UL2	UL3	L+A	L+E	L-A/E	Signal	L+	L-										

	Datum letzte Aend.	05.06.2014
	Letzter Bearbeiter	Hong-Phat Le
	Erstelldatum	02.04.2014
Index	Rev. Bezeichnung	Ersteller
		Hong-Phat Le



Überstromrichtungszeitschutz wandlerstrombetätigt Anschaltungsbeispiel

Projektnummer:	&EFA =	=
Anmerkungen:	VARIANTE B14/2	+ B14 / 2
		Blatt von 56