

Article

2700074

 from revision

03

 Designation

ILC 191 ME/AN

Device category 3 - electrical article

Prediction done by: pylt02

				based on	Environmental condition	MTTF in h	MTTF in a	failure rate in FIT (λ basis)
at	25	°C with	21,00 % duty cycle	SN 29500	GB, GC - Ground Benign, Controlled	1.803.214	205,85	554,565262
at	40	°C with	34,25 % duty cycle	SN 29500	GB, GC - Ground Benign, Controlled	839.427	95,83	1191,288222
at	55	°C with	100,00 % duty cycle	SN 29500	GB, GC - Ground Benign, Controlled	183.571	20,96	5447,483905
at		°C with	% duty cycle			-	-	
at		°C with	% duty cycle			-	-	
at		°C with	% duty cycle			-	-	