

# TMP-UCT-MAG1 - Magazine



0803342

<https://www.phoenixcontact.com/us/products/0803342>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-TM..., UCT1(U)-TM..., UCT5-TM..., UCT-EM (5x10), UCT-EM (6x10), length: 0.166 m, width: 114 mm, height: 11.5 mm



The figure shows version

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0803342       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BG03          |
| Product key                          | BG122Z        |
| GTIN                                 | 4055626041858 |
| Weight per piece (including packing) | 398.3 g       |
| Weight per piece (excluding packing) | 394 g         |
| Customs tariff number                | 84439990      |
| Country of origin                    | DE            |

# TMP-UCT-MAG1 - Magazine



0803342

<https://www.phoenixcontact.com/us/products/0803342>

## Technical data

### Product properties

|              |          |
|--------------|----------|
| Product type | Magazine |
|--------------|----------|

### Dimensions

|        |         |
|--------|---------|
| Width  | 114 mm  |
| Height | 11.5 mm |
| Depth  | 9.5 mm  |
| Length | 166 mm  |

### Material specifications

|                |     |
|----------------|-----|
| RoHS compliant | yes |
|----------------|-----|

### Environmental and real-life conditions

#### Ambient conditions

|                                |   |
|--------------------------------|---|
| Recommended storage conditions | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |
|--------------------------------|---|

0803342

<https://www.phoenixcontact.com/us/products/0803342>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 19140615 |
| ECLASS-15.0 | 19140615 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001675 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 43211600 |
|-------------|----------|

## Environmental product compliance

### EU RoHS

|   |   |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 1.478 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)