

# TMP-RIBBON 110 RD 100 - Ink ribbon cartridge



0803377

<https://www.phoenixcontact.com/us/products/0803377>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)..., US-TM(F)L..., US-WMTB..., US-EML..., US-EML(S)P..., US-EMLP-HA..., US-EM(S)P..., US-EML-RS..., roll length: 60 m, width: 110 mm



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0803377       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BG02          |
| Product key                          | BG1223        |
| GTIN                                 | 4055626042169 |
| Weight per piece (including packing) | 213 g         |
| Weight per piece (excluding packing) | 166 g         |
| Customs tariff number                | 96121010      |
| Country of origin                    | FR            |

# TMP-RIBBON 110 RD 100 - Ink ribbon cartridge



0803377

<https://www.phoenixcontact.com/us/products/0803377>

## Technical data

### Product properties

|              |            |
|--------------|------------|
| Product type | Ink ribbon |
|--------------|------------|

### Marking

|                           |                  |
|---------------------------|------------------|
| Identification technology | Thermal transfer |
|---------------------------|------------------|

### Dimensions

|                |        |
|----------------|--------|
| Width          | 110 mm |
| Length of roll | 60 m   |

### Material specifications

|          |                |
|----------|----------------|
| Color    | red (RAL 3001) |
| Material | Polyester      |

### Environmental and real-life conditions

#### Ambient conditions

|   |      |
|---|------|
| Recommended ambient temperature (storage/transport) | 5 °C |
| Recommended humidity (storage/transport)            | 30 % |

# TMP-RIBBON 110 RD 100 - Ink ribbon cartridge



0803377

<https://www.phoenixcontact.com/us/products/0803377>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 19140614 |
| ECLASS-15.0 | 19140614 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001694 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 44103100 |
|-------------|----------|

# TMP-RIBBON 110 RD 100 - Ink ribbon cartridge



0803377

<https://www.phoenixcontact.com/us/products/0803377>

## Environmental product compliance

### EU RoHS

|   |   |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)