

TMP/EXT.POWER-SUPPLY 100-240V - Power supply unit



0803672

<https://www.phoenixcontact.com/us/products/0803672>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement power supply for THERMOMARK PRIME, input voltage at 100 V AC to 240 V AC / 1.5 A / 50 Hz to 60 Hz, output voltage at 24 V DC / 4.16 A



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0803672 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG03 |
| Product key | BG122Z |
| GTIN | 4055626247779 |
| Weight per piece (including packing) | 1,084.5 g |
| Weight per piece (excluding packing) | 1,084.5 g |
| Customs tariff number | 85044083 |
| Country of origin | DE |

TMP/EXT.POWER-SUPPLY 100-240V - Power supply unit



0803672

<https://www.phoenixcontact.com/us/products/0803672>

Technical data

Product properties

Product type

Printing system accessories

TMP/EXT.POWER-SUPPLY 100-240V - Power supply unit




0803672


<https://www.phoenixcontact.com/us/products/0803672>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0803672>

 **UL Listed**
Approval ID: E140403

 **cUL Listed**
Approval ID: E140403

 **EAC**
Approval ID: KZ 27978

TMP/EXT.POWER-SUPPLY 100-240V - Power supply unit



0803672

<https://www.phoenixcontact.com/us/products/0803672>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19140192 |
| ECLASS-15.0 | 19140192 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001675 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43211600 |
|-------------|----------|

TMP/EXT.POWER-SUPPLY 100-240V - Power supply unit



0803672

<https://www.phoenixcontact.com/us/products/0803672>

Environmental product compliance

EU RoHS

| | |
|---|--------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-10 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com