

# SD-WMS 10 (SY)R RD:+ - Wire marking tag



0826336:+

<https://www.phoenixcontact.com/us/products/0826336:+>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, labeled with the symbol: Symbols, red, mounting type: thread on

## Commercial data

Item number	0826336:+
Packing unit	250 pc
Minimum order quantity	250 pc
Product key	BG2221
GTIN	4046356425735
Weight per piece (including packing)	0.235 g
Weight per piece (excluding packing)	0.235 g
Country of origin	SE

# SD-WMS 10 (SY)R RD:+ - Wire marking tag



0826336:+

<https://www.phoenixcontact.com/us/products/0826336:+>

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Printing	Symbols
Slot type	Profile

### Dimensions

Width	4.2 mm
Height	9.5 mm
Length	6.60 mm

### External dimensions

Outside diameter	4 mm ... 10 mm
------------------	----------------

### Material specifications

Color	red
Material	Polyvinyl chloride
Flammability rating according to UL 94	V0
Components	Free from silicone and cadmium

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Mounting

Mounting type	thread on
---------------	-----------

# SD-WMS 10 (SY)R RD:+ - Wire marking tag



0826336:+

<https://www.phoenixcontact.com/us/products/0826336:+>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)