

EMT (38X25)R /OS - Device marker



0832081

<https://www.phoenixcontact.com/us/products/0832081>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device marker, unmarked, mounting type: snapped into marker carrier, text field height: 25 mm, text field width: 38 mm

Your advantages

- EMT ... insert labels for labeling various marking collars
- Thanks to their special shape, EMT ... insert labels remain securely inside the collar once inserted
- Quick and inexpensive marking with THERMOMARK ... roll printers from Phoenix Contact
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- Marking service: Phoenix Contact can custom-mark all EMT ... markers according to your requirements

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0832081 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG16 |
| Product key | BG2411 |
| GTIN | 4046356986953 |
| Weight per piece (including packing) | 675.6 g |
| Weight per piece (excluding packing) | 675.6 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

EMT (38X25)R /OS - Device marker



0832081

<https://www.phoenixcontact.com/us/products/0832081>

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Device marker |
|--------------|---------------|

Dimensions

| | |
|--------|----------|
| Width | 25.00 mm |
| Height | 38.00 mm |
| Depth | 0.18 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 38 mm |
| Text field height | 25 mm |

Material specifications

| | |
|-----------------------|-----------|
| Base element material | Polyester |
|-----------------------|-----------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

Wipe resistance of inscriptions

| | |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

Mounting

| | |
|---------------|-----------------------------|
| Mounting type | snapped into marker carrier |
|---------------|-----------------------------|

EMT (38X25)R /OS - Device marker



0832081

<https://www.phoenixcontact.com/us/products/0832081>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281106 |
| ECLASS-15.0 | 27281106 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131504 |
|-------------|----------|

EMT (38X25)R /OS - Device marker



0832081

<https://www.phoenixcontact.com/us/products/0832081>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com