

FBST 500 TMC-N GY - Continuous plug-in bridge



0901028

<https://www.phoenixcontact.com/us/products/0901028>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Continuous plug-in bridge, mounting type: Plug-in mounting

Commercial data

Item number	0901028
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	CL04
Product key	CLA19Z
GTIN	4046356318006
Weight per piece (including packing)	121.2 g
Weight per piece (excluding packing)	116.9 g
Customs tariff number	85366990
Country of origin	DE

FBST 500 TMC-N GY - Continuous plug-in bridge



0901028

<https://www.phoenixcontact.com/us/products/0901028>

Technical data

Product properties

Product type	Bridge
Type	Plug-in bridge

Material specifications

Color	light gray (RAL 7035)
-------	-----------------------

Mounting

Mounting type	Plug-in mounting
---------------	------------------

FBST 500 TMC-N GY - Continuous plug-in bridge



0901028

<https://www.phoenixcontact.com/us/products/0901028>

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FBST 500 TMC-N GY - Continuous plug-in bridge



0901028

<https://www.phoenixcontact.com/us/products/0901028>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com