

# ZB 5/OG,LGS: 10-100 - Zack marker strip



1050211

<https://www.phoenixcontact.com/us/products/1050211>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, orange (RAL 2003), labeled, printed horizontally: Sets of ten 10 - 100, mounting type: snap into tall marker groove, for terminal block width: 5.2 mm, Number of individual labels: 10

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1050211       |
| Packing unit                         | 1 pc          |
| Sales key                            | BG05          |
| Product key                          | BG2122        |
| GTIN                                 | 4017918015633 |
| Weight per piece (including packing) | 1.04 g        |
| Weight per piece (excluding packing) | 1.04 g        |
| Customs tariff number                | 49119900      |
| Country of origin                    | PL            |

## Technical data

### Notes

|         |   |
|---------|---|
| General | 10 identically marked strips make up one packing unit (PU). |
| General | Diverging technical data. Available on request.             |

### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Terminal marker |
| Pitch        | 5.2 mm          |

### Marking

|                                     |                      |
|-------------------------------------|----------------------|
| Number of individual labels         | 10                   |
| Number of individual labels per row | 10                   |
| Number of marker strips             | 10                   |
| Printing direction                  | printed horizontally |
| Printing                            | Sets of ten 10 - 100 |
| Slot type                           | high                 |

### Dimensions

|        |          |
|--------|----------|
| Width  | 4.60 mm  |
| Height | 10.50 mm |
| Depth  | 4.30 mm  |
| Pitch  | 5.2 mm   |

### Material specifications

|  |                                |
|--|--------------------------------|
| Color                                  | orange (RAL 2003)              |
| Material                               | PA                             |
| Flammability rating according to UL 94 | V2                             |
| Components                             | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|                 | DIN VDE 0611                |

### Mounting

|               |                              |
|---------------|------------------------------|
| Mounting type | snap into tall marker groove |
|---------------|------------------------------|

# ZB 5/OG,LGS: 10-100 - Zack marker strip



1050211

<https://www.phoenixcontact.com/us/products/1050211>

## Classifications

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# ZB 5/OG,LGS: 10-100 - Zack marker strip



1050211

<https://www.phoenixcontact.com/us/products/1050211>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)