

CRIMPFOX-P CC 0.75 L - Crimping pliers



1064998

<https://www.phoenixcontact.com/us/products/1064998>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for COMBICON crimp connectors with cross section: 0.14 ... 0.75 mm².
Unlockable pressure lock, precise parallel crimping, front entry, B crimp, incl. 2 positioning aids

Your advantages

- Female crimp contact PTCM-MP-P...
- Female crimp contact MCC 0,5-MP...
- Precision-manufactured dies ensure consistently high levels of quality during contact processing
- Parallel motion sequences of the dies for symmetrical and optimum crimping results
- PTCM-MP-PI... male crimp contact
- High crimping force with low manual force
- Marked die stations for precise processing of corresponding cross sections

Commercial data

Item number	1064998
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3136
GTIN	4055626722979
Weight per piece (including packing)	530.7 g
Weight per piece (excluding packing)	530.7 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-P CC 0.75 L - Crimping pliers



1064998

<https://www.phoenixcontact.com/us/products/1064998>

Technical data

Product properties

Product type	Crimping tool
Compression	B crimp
Product property	Symmetrical crimping shape due to parallel pliers movement
	Marked die stations

Crimping position 1

Max. cross section	0.34 mm ²
AWG max	22

Crimping position 2

Max. cross section	0.5 mm ²
AWG max	20

Crimping position 3

Max. cross section	0.75 mm ²
AWG max	18

Crimping position 4

Min. cross section	0.14 mm ²
Max. cross section	0.25 mm ²
AWG min	26
AWG max	24

Connection data

Conductor connection

Cross section range, metric	0.14 mm ² ... 0.75 mm ²
Cross section range AWG	26 ... 18

Dimensions

Length	233 mm
--------	--------

Material specifications

Color	black
-------	-------

CRIMPFOX-P CC 0.75 L - Crimping pliers



1064998

<https://www.phoenixcontact.com/us/products/1064998>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1064998>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-P CC 0.75 L - Crimping pliers



1064998

<https://www.phoenixcontact.com/us/products/1064998>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-P CC 0.75 L - Crimping pliers



1064998

<https://www.phoenixcontact.com/us/products/1064998>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com