

CEC UBAL 150 - Cover plate

1086474

<https://www.phoenixcontact.com/us/products/1086474>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover plate, color: yellow



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1086474 |
| Packing unit | 25 pc |
| Minimum order quantity | 25 pc |
| Sales key | BE19 |
| Product key | BE1Z1X |
| GTIN | 4055626878478 |
| Weight per piece (including packing) | 3.6 g |
| Weight per piece (excluding packing) | 3.6 g |
| Customs tariff number | 39269097 |
| Country of origin | EE |

CEC UBAL 150 - Cover plate

1086474

<https://www.phoenixcontact.com/us/products/1086474>



Technical data

Product properties

| | |
|--------------|-----------|
| Product type | End cover |
|--------------|-----------|

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -60 °C ... 85 °C |
| Ambient temperature (storage/transport) | -25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Material specifications

| | |
|--|-------------------|
| Color | yellow (RAL 1018) |
| Flammability rating according to UL 94 | V2 |

CEC UBAL 150 - Cover plate



1086474

<https://www.phoenixcontact.com/us/products/1086474>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281107 |
| ECLASS-15.0 | 27281107 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001777 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CEC UBAL 150 - Cover plate



1086474

<https://www.phoenixcontact.com/us/products/1086474>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.099 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com