

VAH - Cover profile carrier

1201468

<https://www.phoenixcontact.com/us/products/1201468>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Adjustable cover holder, for mounting covers (up to 3 mm thick) on terminal blocks, can be used for CLIPFIX 35 and E/UK

Your advantages

- Large-surface labeling with AP-ES insert strips
- Cover profiles provide protection against unauthorized actuation of terminal strips

Commercial data

Item number	1201468
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE07
Product key	BE61ZX
GTIN	4017918017347
Weight per piece (including packing)	8.13 g
Weight per piece (excluding packing)	7.4 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Product type	Cover profile
--------------	---------------

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V2
Static insulating material application in cold	-40 °C
Relative insulation material temperature index (Elec., UL 746 B)	125 °C

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

VAH - Cover profile carrier


1201468

<https://www.phoenixcontact.com/us/products/1201468>



Drawings

Dimensional drawing



VAH - Cover profile carrier

1201468

<https://www.phoenixcontact.com/us/products/1201468>



Classifications

ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

ETIM

ETIM 10.0	EC002886
-----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

VAH - Cover profile carrier

1201468

<https://www.phoenixcontact.com/us/products/1201468>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.031 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com