

NS 15 PERF 1000MM - DIN rail perforated



1207646

<https://www.phoenixcontact.com/us/products/1207646>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail perforated, acc. to EN 60715, length: 1000 mm, material: Steel, galvanized, passivated with a thick layer, mounting type: Standard profile, color: silver-colored, Current dimensional tolerances: Profile tolerance due to burr/sharp edges = ± 0.5 mm, Initial dimension = ± 0.5 mm, Hole pattern = ± 0.5 mm, Hole position = ± 0.5 mm, Minimum rail length: Unperforated: > 20 mm, Perforated: > 100 mm, Last punching at Phoenix Contact: < 1750 mm

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1207646 |
| Packing unit | 20 pc |
| Minimum order quantity | 20 pc |
| Sales key | BH84 |
| Product key | BH8421 |
| GTIN | 4046356366045 |
| Weight per piece (including packing) | 999 g |
| Weight per piece (excluding packing) | 999 g |
| Customs tariff number | 72166190 |
| Country of origin | DE |

NS 15 PERF 1000MM - DIN rail perforated



1207646


<https://www.phoenixcontact.com/us/products/1207646>

Technical data

Product properties

| | |
|--------------|----------|
| Product type | DIN rail |
|--------------|----------|

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 15 mm |
| Hole width | 12.2 mm |
| Hole height | 4.2 mm |
| Depth | 5.5 mm |
| Length | 1000 mm |
| Drill hole spacing | 20 mm |
| Hole diameter | 4.2 mm ... 12.2 mm |

Material specifications

| | |
|----------|---|
| Color | silver-colored |
| Material | Steel |
| Coating | galvanized, passivated with a thick layer |

Standards and regulations

| | |
|----------------------------------|------------------|
| Connection in acc. with standard | IEC / EN |
| Tests | acc. to EN 60715 |

Electrical tests

| | |
|----------------------------------|--------------------|
| Short-time withstand current | |
| Equivalent E-Cu cross-section | 10 mm ² |
| Short-time current resistance 1s | 1.2 kA |

NS 15 PERF 1000MM - DIN rail perforated


1207646

<https://www.phoenixcontact.com/us/products/1207646>



Drawings

Dimensional drawing



NS 15 PERF 1000MM - DIN rail perforated



1207646

<https://www.phoenixcontact.com/us/products/1207646>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27400602 |
| ECLASS-15.0 | 27400602 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001285 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

NS 15 PERF 1000MM - DIN rail perforated



1207646

<https://www.phoenixcontact.com/us/products/1207646>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com