

CRIMPFOX-RC 10 - Crimping pliers



1212061

<https://www.phoenixcontact.com/us/products/1212061>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for non-insulated cable lugs, 4 ... 10 mm², double indent crimp

Your advantages

- The CRIMPFOX-RC 10 completes the range of crimping pliers for uninsulated cable lugs and insulated tube lugs
- All pliers of this design reduce the amount of force required for crimping by 25%

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212061 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3133 |
| GTIN | 4046356453936 |
| Weight per piece (including packing) | 660.205 g |
| Weight per piece (excluding packing) | 660.2 g |
| Customs tariff number | 82032000 |
| Country of origin | SE |

CRIMPFOX-RC 10 - Crimping pliers



1212061

<https://www.phoenixcontact.com/us/products/1212061>

Technical data

Notes

Environmental Product Compliance

| | |
|---------------------------|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---|

Product properties

| | |
|------------------|---------------------------------|
| Product type | Crimping tool |
| Compression | Indent crimp |
| Product property | Indent crimp |
| | Up to 25% lower actuation force |

Crimping position 1

| | |
|--------------------|-------------------|
| Max. cross section | 4 mm ² |
| AWG max | 12 |

Crimping position 2

| | |
|--------------------|-------------------|
| Max. cross section | 6 mm ² |
| AWG max | 10 |

Crimping position 3

| | |
|--------------------|--------------------|
| Max. cross section | 10 mm ² |
| AWG max | 8 |

Connection data

Conductor connection

| | |
|-----------------------------|--|
| Cross section range, metric | 4 mm ² ... 10 mm ² |
| Cross section range AWG | 12 ... 8 |

Dimensions

| | |
|--------|--------|
| Width | 25 mm |
| Height | 68 mm |
| Length | 256 mm |

Material specifications

| | |
|-------|-------|
| Color | black |
|-------|-------|

CRIMPFOX-RC 10 - Crimping pliers



1212061

<https://www.phoenixcontact.com/us/products/1212061>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212061>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-RC 10 - Crimping pliers



1212061

<https://www.phoenixcontact.com/us/products/1212061>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043811 |
| ECLASS-15.0 | 21043811 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000168 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CRIMPFOX-RC 10 - Crimping pliers



1212061

<https://www.phoenixcontact.com/us/products/1212061>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com