

CUTFOX-SP VDE - Diagonal cutter



1212206

<https://www.phoenixcontact.com/us/products/1212206>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power diagonal cutter, with optimized leverage, also suitable for piano wire, VDE 1000 V AC/1500 V DC tested

Your advantages

- Precision cutting edge for piano wire
- VDE tested
- Special tool steel for permanent use
- Ergonomically shaped two-component handles for fatigue-free and non-slip use
- Cutting harder materials with minimal effort due to high leverage

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212206 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH311S |
| GTIN | 4046356454223 |
| Weight per piece (including packing) | 318 g |
| Weight per piece (excluding packing) | 300 g |
| Customs tariff number | 82032000 |
| Country of origin | DE |

CUTFOX-SP VDE - Diagonal cutter



1212206

<https://www.phoenixcontact.com/us/products/1212206>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

| | |
|------------------|--|
| Product type | Cutting tool |
| Application | Aluminum |
| | Copper |
| | Piano wire |
| Product property | Inductively hardened precision cutting edge |
| | Ergonomic two-component handle |
| | Optimized leverage |
| | Special tool steel, die-forged and oil-hardened\ |
| | ~ 62 HRc |
| | VDE tested |

Dimensions

| | |
|--------|--------|
| Length | 200 mm |
|--------|--------|

Material specifications

| | |
|-------|----------------------|
| Color | multicolored (RAL -) |
|-------|----------------------|

Cable/line

| | |
|-------------------------|-----------------|
| External cable diameter | ≤ 4.00 mm |
| | 0.2 mm ... 4 mm |

Standards and regulations

| | |
|-------|----------------------------------|
| Tests | DIN EN 60900 (VDE 0682 PART 201) |
| | DIN ISO 5746 |

CUTFOX-SP VDE - Diagonal cutter



1212206

<https://www.phoenixcontact.com/us/products/1212206>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212206>



EAC

Approval ID: RU x-DE.xx08.B.02974



VDE approval of drawings

Approval ID: 40052526

CUTFOX-SP VDE - Diagonal cutter



1212206

<https://www.phoenixcontact.com/us/products/1212206>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043711 |
| ECLASS-15.0 | 21043711 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000165 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CUTFOX-SP VDE - Diagonal cutter



1212206

<https://www.phoenixcontact.com/us/products/1212206>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 4.317 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com