

MICROFOX-PC ESD - Needle-nose pliers



1212483

<https://www.phoenixcontact.com/us/products/1212483>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



ESD electronic needle-nose pliers, 45° angle, smooth grip, with opening spring, non-reflective coating and phosphate-treated, two-component grip

Product description

Note:
Due to the current challenges of the global procurement market, Phoenix Contact has unfortunately been forced to accept a different ESD-compliant material. In future, the tools will be supplied with plastic handles in black/turquoise. This does not affect the function or quality of the ESD pliers.

Your advantages

- Through-connected joint for permanent stability and optimum distribution of force
- Opening spring for uniform, smooth opening
- Ergonomically shaped two-component handles for fatigue-free and non-slip use
- Special conductive plastic handles for slow and controlled dissipation of electrostatic energy
- Special tool steel for permanent use
- Mirror-polished and phosphate-treated metal surfaces for optimum rust protection and no glare when working

Commercial data

Item number	1212483
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3152
GTIN	4046356527156
Weight per piece (including packing)	89.5 g
Weight per piece (excluding packing)	89.5 g
Customs tariff number	82032000
Country of origin	DE

MICROFOX-PC ESD - Needle-nose pliers



1212483

<https://www.phoenixcontact.com/us/products/1212483>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Electronics pliers
Product property	Uniform and smooth opening
	Ergonomically designed handle
	Two-component handle
	Push-through joint
	Mirror-polished and phosphated metal surfaces
	ESD tested

Electrical properties

Fuse	DIN EN 61340-5-1/VDE 0300-5-1, DIN EN 61340-2-3/VDE 0300-2-3
------	--

Dimensions

Width	60 mm
Height	7 mm
Length	130 mm

Material specifications

Color	multicolored (RAL -)
Material	Steel
Coating	phosphatized

MICROFOX-PC ESD - Needle-nose pliers



1212483

<https://www.phoenixcontact.com/us/products/1212483>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212483>



EAC

Approval ID: RU x-DE.xx08.B.02974

MICROFOX-PC ESD - Needle-nose pliers



1212483

<https://www.phoenixcontact.com/us/products/1212483>

Classifications

ECLASS

ECLASS-13.0	21043816
ECLASS-15.0	21043816

ETIM

ETIM 10.0	EC000835
-----------	----------

UNSPSC

UNSPSC 21.0	27112100
-------------	----------

MICROFOX-PC ESD - Needle-nose pliers



1212483

<https://www.phoenixcontact.com/us/products/1212483>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	3.29 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com